PIERLITE®

IPART VEET

Slimline Oyster Gen3

SL24W3/4/57KDG3

- A round LED luminaire with a classic trim and diffused optics for glare free homogenous lighting. The Slimline Gen3 has a back light halo feature producing that perfect ambience.
- Modern and sleek low profile design when aesthetics is important.
- 25mm cable entry with large PA12 terminals and a new push-to-lock feature for ease of installation.

LUMEN SELECT™ | COLOUR SELECT

Performance

System Power	24W, 17W
Exit Lumen	2374lm, 1754lm, 1812lm, 1770lm, 2501lm, 2409lm
Efficacy	100lm/W
CCT	3000K, 4000K, 5700K
CRI	80
Operating Temperature	0 to 40
MacAdam Steps	6SDCM
Ingress Protection Rating	IP54
Impact Rating	IK03
Warranty	5 Years
Lifetime	60,000hrs (L70/B50) @ 40ºC

Physical

Dimensions	Ø400 x H36 mm
Diffuser	Opal
Luminaire Colour	White
Weight	1.3kg
Luminaire Material	Plastic (Polycarbonate)
Driver Location	Integrated
Installation	Surface Mounting

Electrical

Dimming	Phase
Voltage	240V
Line Voltage Frequency	50Hz
Inrush Current	5A
Inrush Current Duration	21µs
Line Current	0.11A
Electrical Rating	Class II

Line Drawings



SL24W3/4/57KDG3

Product Images



Product Images



*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply