Stingray 2 LED Exit Light

STLED-L



- Ceiling mount and wall mount
- Complete with replaceable lithium iron phosphate (LiFeP04) battery
- Optional IP65 KIT (See datasheet for Aqualock)

Performance

System Power	4.6W
Exit Lumen	124lm
Operating Temperature	0 to 40
Ingress Protection Rating	IP20
Warranty	3 Years
Lifetime	50,000hrs (L70/B50)

Physical

Dimensions	L395 x W81 x H245 mm
Diffuser	Acrylic
Luminaire Colour	White
Weight	1.2kg
Luminaire Material	Plastic (Acrylic)
Driver Location	Integrated
Finish	White
Installation	Ceiling Surface Mounted

Emergency

Emergency Version	Yes
Option	Maintained
Testing System	Manual
Battery	LiFePO4
Battery Voltage	3.2V
Battery Capacity	1500mA
Emergency Mode Wattage	1W
Emergency Mode Lumen	27lm
Classification	C0/C180:D3.2 C90/C270:E2 (2HR)
Battery Charge	2hr
Viewing Distance	24m


Electrical

Voltage	240V
Electrical Rating	Class 1

AS/NZS 2293.1:2018 Classification Table

ALLOWABLE LUMINAIRE MOUNTING HEIGHT (M)	LUMINAIRE MAXIMUM SPACING FOR EACH PLAN (M)	
	C0/180	C90/C270
2.1	6.5	5
2.4	6.5	5.2
2.7	6.5	5.2

Line Drawings



Accessories

LEDRB	RECESSED BRACKET KIT WHITE
EXCB	EXCB BRKT EXIT W/MOUNT KIT
BATPK1500/1L11	LiFePO4, battery pack 1 CELL3.2V 1500mAh
AQUALOCK-W	AQUALOCK W/PROOF EXIT ENCLOSURE WH/BASE

*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply

Pierlite is a division of Signify Innovations Australia Pty Ltd