Stingray Exit Light Gen3

STINGBKG3

- Suitable for both ceiling and wall mounting
- Replaceable lithium iron phosphate (LiFeP04) battery
- Features manual testing and maintained emergency exit functionality, complete with all pictogram inserts



Performance

System Power	4.2W
Operating Temperature	0 to 40
Ingress Protection Rating	IP20
Warranty	5 Years
Lifetime	50,000hrs (L70/B10)

Physical

Dimensions	L399.80 x W81.50 x H249 mm
Diffuser	Polycarbonate
Luminaire Colour	Black
Weight	1.7kg
Luminaire Material	Plastic (Polycarbonate)
Finish	Black
Installation	Ceiling or Wall Mounting


Emergency

Emergency Version	Yes
Option	Maintained
Testing System	Self-Test or DALI2 Monitoring
Battery	LiFePO4
Battery Voltage	6.4V
Battery Capacity	1500mA
Emergency Mode Wattage	4.2W
Battery Charge	2hr
Viewing Distance	24m

Electrical

Voltage	240V
Line Voltage Frequency	50Hz
Inrush Current	20A
Inrush Current Duration	140µs
Line Current	0.04A
Electrical Rating	Class II

Line Drawings



Product Images



Accessories

BLADEPROSUSKITWH	Rod and Wire Mounted Kit (Rod and wire excluded)
DGLCEM3200/1L11	Battery LiFePO4 1 Cell 3.2V 3200mAh

Product Images





*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply