Tablet Wall Light

TABL830BG3

- Sturdy and robust design - made with die-cast aluminium, frosted glass diffuser and stainless-steel screws
- Easy to install - rear cable entry with large terminal blocks
- Ideal for residential, domestic and hospitality exterior applications



Performance

System Power	4W
Exit Lumen	370lm
Efficacy	92lm/W
CCT	3000K
CRI	80
Operating Temperature	0 to 40
Ingress Protection Rating	IP65
Impact Rating	IK06
Warranty	5 Years
Lifetime	50,000hrs (L70/B50)


Physical

Dimensions	L170.50 x W94.60 x H59.50 mm
Diffuser	Frosted Glass
Luminaire Colour	Black
Weight	0.62kg
Luminaire Material	Aluminium (Die Cast)
Driver Location	Integrated
Finish	Powder Coated
Installation	Wall Surface Mounted

Electrical

Voltage	240V
Line Voltage Frequency	50Hz/60Hz
Inrush Current	15A
Inrush Current Duration	200µs
Line Current	25A
Electrical Rating	Class 1

Line Drawings



Product Images



Product Images





*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply

Pierlite is a division of Signify Innovations Australia Pty Ltd