Tablet Wall Light

TABLDI830BG3

- Sturdy and robust design - made with die-cast aluminium, frosted glass diffuser and stainless-steel screws
- Easy to install - rear cable entry with large terminal blocks
- Ideal for residential, domestic and hospitality exterior applications



COLOUR SELECT

Performance

System Power	7W
Exit Lumen	708lm, 758lm, 756lm
Efficacy	101lm/W
CCT	3000K, 4000K, 5000K
CRI	80
Operating Temperature	0 to 40
Ingress Protection Rating	IP65
Impact Rating	IK06
Warranty	5 Years
Lifetime	50,000hrs (L70/B50)


Physical

Dimensions	L170.50 x W94.60 x H59.50 mm
Diffuser	Frosted Glass
Luminaire Colour	Black
Weight	0.69kg
Luminaire Material	Aluminium (Die Cast)
Driver Location	Integrated
Finish	Powder Coated
Installation	Wall Surface Mounted

Electrical

Voltage	240V
Inrush Current	15A
Inrush Current Duration	200µs
Line Current	25A
Electrical Rating	Class 1

Line Drawings



Product Images



Product Images





*Rated LED design life where stated is based upon application of Pierlite's operating and maintenance guidelines; see pierlite.com.au. Actual product life may vary dependent upon frequency of maintenance and product application. Due to continual product improvement, information is subject to change without notification.
standard Terms and Conditions apply

Pierlite is a division of Signify Innovations Australia Pty Ltd