

Office Lum/LED办公灯具

RC650B

Mounting instruction/安装说明书

444170265951



$t_a 25^\circ\text{C}$



IP 20




CB



Type	Voltage	Frequency	Power	Dimension LxWxH (cm)	kg
型号描述 RC650B LED40S PSU W60L60 TWN	电压 100-277V~	频率 50/60Hz	功率 35W	灯具尺寸 LxWxH (cm) 59.7x59.7x7	5.3

CRI80 and CRI90

RC650B W60L60:



Accessories for Optional/可选附件

Type Desc	Accessories Desc
RC650Z PCV ACC W60L60	Mounting accessory for PCV/石膏板安装附件

只有台湾有用：限用物質含有情況標示資訊請參考昕諾飛網址

<http://www.philips.com/lighting>

說明：請點選頁面中[支援]清單下之[RoHS資訊]標籤

Inrush current

Product Type	Run Current (A) (@220V)	Start (Inrush) Current(A) / Ipeak (A)	Start Current Duration (μs) / T(@50% of Ipeak) (μs)	Touch current or protective conductor current (mA)	MCB Type B 16A (or Type C 16A) Max no. fitting (pcs)
RC650B LED40S PSU W60L60 TWN	0.163	I2.60	176	0.7	≤24

1. 灯具应由有资格的电工安装，接线要符合IEE 电气标准或国家标准。
2. 接线过程中，切勿通电。
3. 灯具适合于直接安装在普通可燃材料表面。
4. 仅限于室内使用。
5. 灯具避免在腐蚀性环境或者含有有害物质，例如硫化物，卤化物，邻苯二甲酸酯等环境中存储和使用。
6. 此灯具内的光源应由制造商或其服务代理商或一个有类似资格的人来更换。
7. 可控灯具产品中，LV电路和控制导体之间是基本绝缘。
8. 此灯具不适合被隔热衬垫或类似材料覆盖。
9. 不得使用酸性或碱性清洗剂清洗灯具。不得使用在腐蚀PC的应用环境，例如乙胺、四氯乙烯等。
10. 如发现异常或操作有任何问题，请务必先切断电源，然后与飞利浦经销商联系。
11. 灯具的使用和储存必须在允许的应用环境内。
12. 本产品防护等级为IPX0，不能防止进水，强烈建议安装本产品前对使用环境的适应性进行检查评估。
一但有进水，产品可能会发生电气故障或安全事故，飞利浦/昕诺飞对此不承担质保责任。



1. Indoor use only.
2. Do not switch on before complete installation.
3. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
4. The luminaire shall, under no circumstance, be covered with insulation matting or similar material.
5. The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
6. Luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, phthalates, etc, are present.
7. For controllable luminaires, basic insulation has been maintained between LV supply and control conductors.
8. The luminaire shall, under no circumstance, be covered with thermal insulation matting or similar material.
9. Do not use acid or alkaline cleaner to clean this luminaire. Do not use this luminaire in the environment that will corrode PC, for example ethylamine, tetrachloroethylene etc.
10. If any abnormal to be found or operation problem. Be sure switch off the power first and contact your nearest Philips dealer.
11. The Luminaire must be used within the applicable product specifications, installation instructions and environmental conditions for storage & operations according to application guidelines provided by Philips for product Warranty to be valid.
12. The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked if the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void.

Signify (China) Investment Co., Ltd.

Building No. 9, Lane 888 Tianlin Road, Minhang District, Shanghai, China

Postalcode: 200233

昕诺飞(中国)投资有限公司

中国上海市闵行区田林路888弄9号楼

邮编: 200233


PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

T-bar Installation / T-bar 安装

I-1

Recessed / 嵌入安装




A



B



C




PCV Installation / PCV 安装

I-2



A 石膏板开孔尺寸 Cutout Size

W60L60: 627x627mm(+/- 2mm)

B



C




Rest steps same as T-bar mounting / 其余步骤同T-bar安装


2

Safety chain via hook / 安装安全链

A



B



Safety chain is not included.

Customers need to buy separately.

本产品不含安全吊链,客户需单独购买。


3

Connect Entry cable / 连接电源线

Please connect the cable to the terminal box (IP20 or above), then place the terminal box into the ceiling.
请使用IP20以上的接线盒,接线完成后将接线盒放置到天花内,不提供接线盒。

Luminaire cable/电源线:
60245 IEC53 3x0.75 mm

Luminaire cable:
60245 IEC53 3x0.75 mm (PSU)
L: Brown;
N: Blue;
⏚: Yellow+Green



Remark: Terminal box is not provided. 注意: 接线盒不含在此灯具内。
To reduce the risk of strangulation the flexible wiring connected to this luminaire shall be effectively fixed to the wall if the wiring is within arm's reach