


# SmartBright Slim Panel

RC091V

Mounting instruction/安装说明书

V1.0



Product Type 产品型号	Power 功率	Lumen Output 流明输出	Energy efficiency class 能效等级	CCT 色温	kg
RC091V LED30S PSU W60L60	30W	3000lm	3级	840 : 4000 K	1.75
RC091V LED30S PSU W30L120	30W	3000lm			1.75
RC091V LED50S PSU W60L120	50W	5000lm		4.0	
RC091V LED30S PSU W20L12	30W	3000lm		1.25	

Unit/单位:mm

	L	W	H
W60L60	597	597	33
W30L120	1197	297	33
W60L120	1197	597	33
W60L60 CPC	600	600	33
W30L120 CPC	1200	300	33
W20L120	1197	597	33

Wiring Method/接线方式

2x0.75mm<sup>2</sup>  
L: Brown/棕色  
N: Blue/蓝色

请使用IP20或以上的接线盒  
(接线端子尺寸不小于10x20x25)  
它不包含在包装里面。

Unit/单位:mm



Available as accessory(Need to purchase separately)/可选附件需另外购买

Plaster ceiling set/石膏板安装附件 911401824580 RCO48Z SMB-PLC	Suspension set/悬吊安装附件 911401824680 RCO48Z SME-2	Surface mounted set/表面安装附件 911401867182:Panel SMB W60L60 H7 911401867282:PanelSMB W30L 20 H7	Safety cable/安全绳 911401824780:RCO48Z SC (W60L60/W30L120)	Safety cable/安全绳 911401809187:RC159Z (W60L120)

**A Visible Profile Ceiling Mounting (VPC) 嵌入式安装**

**B Plaster Ceiling Version Mounting (PCV) 石膏板安装**  
Optional with 911401824580 RCO48ZSMB-PLC

开孔尺寸/Cutout size(mm)  
W60L60:580x580(+/-2)  
W30L120:280x1180(+/-2)  
W20L120:180x1180(+/-2)

8 - 16mm

These 4 clips are not included in the package.  
这4个弹簧夹不包含在包装里

Signify Luminaires (Shanghai) Co., Ltd.  
Address: 2F, Building 1, No.2555, Hechuan Road, Minhang District, Shanghai City, P.R.China  
China Postal code: 200233  
昕诺飞灯具(上海)有限公司  
地址: 上海市闵行区合川路2555号1幢二楼  
邮编: 200233



# PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

**C Concealed Profile Ceiling (CPC)集成吊顶安装**

Unit/单位:mm

W60L120: Thickness must be > 0.3mm when installing the keel, safety rope assembly must be added (product includes safety rope)  
W60L120: 安装龙骨时厚度必须>0.3mm, 必须增加安全吊绳装配(产品包含安全吊绳)

**D Suspension Mounting/(SUS)悬吊安装**  
Optional with 911401824680 RCO48Z SME-2

Ca.100mm-1450mm

The suspension wires are not included in package.  
悬吊绳不包含在包装里。

**E Safety cable/安全绳**  
911401867182:Panel SMB W60L60 H7  
911401867282:Panel SMB W30L120 H7

The surface mounting accessory is not included in package,  
表面安装框附件不包含在包装里。

**E Safety cable/安全绳**  
Optional with 911401824780 RCO48Z SC

The product should be installed with safety cable. Safety cable is not included in the box,  
it could be ordered by separate I2NC.  
产品必须安装安全电缆。安全电缆不包括在盒子里, 可以单独订购I2NC。  
911401824780 RCO48Z SC for W60L60/W30L120  
911401809187 RC159Z SC for W60L120

Please read this manual carefully before using the product.

- 1.For indoor use only.
- 2.Do not switch on before completing the installation.
- 3.The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- 4.If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
- 5.The luminaire shall not be covered with thermal insulation or similar material under any circumstance.
- 6.The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
- 7.The luminaire is complied with GB/T 7000.1-2023
- 8.The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc, must be avoided during the use and storage.

在使用产品前请仔细阅读这个安装指南:

1. 仅适用于室内灯具;
2. 接线过程中, 切勿通电;
3. 灯具应由有资格的电工安装, 接线要符合IEE电气标准或国家标准;
4. 如果此灯具的外部软缆或软线损坏了, 该线要由制造商或其服务代理商或一个类似的有资格的人来更换以避免发生危险;
5. 灯具不能被隔热或类似材料覆盖;
6. 此灯具内的光源应由制造商或其服务代理商或一个类似的有资格的人来更换;
7. 此灯具是依据国标GB/T 7000.1-2023所制造;
8. 此灯具避免在腐蚀性环境或者含有有害物质, 例如硫化物, 卤化物, 邻苯二甲酸酯等环境中存储和使用。

**用户资料**

用户姓名: \_\_\_\_\_ (先生/女士)

产品名称: \_\_\_\_\_

产品型号: \_\_\_\_\_

出售单位及地址: \_\_\_\_\_

购买日期: 年 月 日

发票号码: \_\_\_\_\_

**PHILIPS**  
Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.

昕诺飞(中国)投资有限公司  
中国上海市闵行区田林路888弄9号楼, 邮编: 200233  
服务热线: 8008 201 201  
4009 201 201

仅限中国大陆地区

**昕诺飞灯具产品**  
质保条款

本公司保证该产品在正常使用及保养下能发挥其优越性能。同时本公司将为持证用户提供一年质保服务(不含光源)。

1. 自购买日起一年内, 凡经本公司确认为正常使用情况下因产品本身质量问题导致的故障及损坏, 您将获得质保服务。
2. 此质保服务包括灯具以及灯具包含的附件、辅助装置。
3. 消费者申请质保服务时, 须提供本保修证以及有效的购买凭证。
4. 以下情况将不能享受质保服务:
  - 1) 非质量问题造成产品外壳严重损坏(包括变形、氧化、腐蚀或有严重的水渍等);
  - 2) 产品已拆封或非本公司授权人员拆卸、改装或修理过;
  - 3) 超过质保有效期的产品;
  - 4) 正常使用引起的产品老化、磨损、划伤、掉漆等, 不影响产品的正常使用;
  - 5) 非质量问题造成产品外壳严重损坏(包括变形、氧化、腐蚀或有严重的水渍等);
  - 6) 使用不当引起的人为损坏, 如接不当电源、使用不当的配件、不适当之安装、不依照说明书使用、错误使用或疏忽造成的损坏等;
  - 7) 其他不可抗力因素, 如火灾、地震、高压、酸碱腐蚀、雷击及涌电等造成的损坏。

服务热线: 8008 201 201  
4009 201 201

昕诺飞(中国)投资有限公司 仅限中国大陆地区

**产品中有害物质的名称及含有信息表**

部件名称	有害物质									
	Pb	Hg	Cd	Cr(VI)或Cr <sup>6+</sup>	PBBs	PBDEs	DBP	DIBP	BBP	DEHP
LED灯板/光源	○	○	○	○	○	○	○	○	○	○
LED控制装置, 铜制及电子零部件	×	○	○	○	○	○	○	○	○	○
外壳, 灯罩及光学部件	○	○	○	○	○	○	○	○	○	○

注1: ○: 表示该有害物质在该部件所有均质材料中的含量均不超过电器电子产品有害物质限制使用国家标准要求。  
注2: ×: 表示该有害物质至少在该部件的某一均质材料中的含量超出电器电子产品有害物质限制使用国家标准要求。  
注3: 以上未列出的部件, 表明其有害物质含量均不超过电器电子产品有害物质限制使用国家标准要求。