




SmartBright Slim Panel RC091V

Mounting Instruction / คู่มือการติดตั้ง



Product Type	Power	Lumen Output	Voltage	CCT	kg
RC091V LED40S PSU W30L120 G4 BCT TH	40W	4000lm	220-240V~	840 : 4000 K	1.9
RC091V LED40S PSU W60L60 G4 BCT TH	40W	4000lm		865 : 6500 K	1.9
RC091V LED50S PSU W60L120 G4 BCT TH	50W	5000lm			3.8

Unit:mm

	L	W	H1	H2
W60L60	597	597	33	8.5
W30L120	1197	297	33	8.5
W60L120	1197	597	33	8.5

Wiring Method

2x0.75mm²
L:Brown N: Blue

Please use IP20 or higher terminal box (Dimension should be 10x20x25 or higher.) It is not included in package.

VPC visible profile ceiling

SP suspended

SM surface mounted

PCV plaster ceiling

Available as accessory(Need to purchase separately)

Plaster ceiling set 911401824580 RCO48Z SMB-PLC 	Suspension set 911401824680 RCO48Z SME-2 	Surface mounted set 911401867182:Panel SMB W60L60 H7 911401867282:Panel SMB W30L120 H7 	Safety cable 911401824780:RCO48Z SC (W60L60/W30L120) 	Safety cable 911401809187:RC159Z (W60L120)
--	---	---	--	--


A Visible Profile Ceiling Mounting(VPC)

B Plaster Ceiling Version Mounting (PCV)

I Cutout size:
 W60L60 : 580x580 mm (+/-)
 W30L120 : 280x1180 mm (+/-)
 W60L120 : 580x1180 mm (+/-)
 Ceiling thickness:
 8mm-16mm


These 4 clips are included in the package.

Signify Luminares (Shanghai) Co., Ltd.
 2F, Building 1, No.2555, Hechuan Road, Minhang District,
 Shanghai City, P.R.China
 China Postal code: 200233





Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.


C Suspension Mounting (SUS)



D Surface mounting



E Safety cable



EN Please read this manual carefully before using the product.

1. For indoor use only.
2. Do not switch on before completing the installation.
3. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
4. If the external flexible cable or cord of this luminaire is damaged, it shall be exclusively replaced by the manufacturer or his service agent or a similar qualified person in order to avoid a hazard.
5. The luminaire shall not be covered with thermal insulation or similar material under any circumstance.
6. The light source in this luminaire shall be replaced by the manufacturer or its service agent or a similarly qualified person;
7. The luminaire is complied with IEC 60598.
8. The corrosive atmosphere or hazardous materials such as sulfur, chlorine, phthalate, etc. must be avoided during the use and storage.



TH โปรดอ่านทำความเข้าใจกับคู่มือก่อนการใช้งานสินค้า

1. ใช้ภายในอาคารเท่านั้น
2. ห้ามเปิดสวิตช์ไฟ หรือจ่ายไฟก่อนติดตั้งเสร็จ
3. ควรติดตั้งคอมโดยช่างไฟฟ้า ซึ่งเป็นไปตามมาตรฐานไฟฟ้า IEE หรือมาตรฐานสากล
4. หากสายไฟที่มาพร้อมคอมเก่า ชำรุด ไม่ควรซ่อม ควรเปลี่ยนใหม่เพื่อความปลอดภัย
5. ไม่ควรนำฉนวนป้องกันอุณหภูมิ หรือวัสดุที่คล้ายกันวางหรือครอบตัวคอม
6. แหล่งกำเนิดแสงภายในคอมไฟนี้ ควรถูกแทน ที่โดยผู้ผลิต หรือตัวแทนบริการ หรือบุคคล ที่มีคุณสมบัติคล้ายกัน
7. คอมไฟรุ่นนี้ เป็นไปตามมาตรฐานสากล IEC60598
8. คอมไฟต้องไม่ถูกติดตั้ง หรือจัดเก็บในสภาพแวดล้อมที่มีสารพิษ หรือสารที่มีเคมีกัดกร่อน เช่น ก๊าซกรด คลอรีน หรือ พาทาเลต (สารเคมีผลิตภัณฑ์พลาสติก)

EN This marking indicates that this product should not be disposed with other household wastes throughout the EU. To prevent possible harm to the environment or human health from uncontrolled waste disposal, recycle it responsibly to promote the sustainable reuse of material resources. To return your used device, please use the return and collection systems or contact the retailer where the product was purchased. They can take this product for environmental safe recycling.



TH เครื่องหมายสัญลักษณ์ที่ระบุว่าสินค้าชนิดนี้ไม่สามารถทิ้งได้เหมือนขยะทั่วไปได้ เพื่อที่จะป้องกันการเกิดอันตรายต่อสภาพแวดล้อมและสุขภาพของมนุษย์จากปัจจัยที่ไม่สามารถควบคุมได้จากขยะมีพิษ การนำมารีไซเคิลอย่างมีความรับผิดชอบที่จะช่วยส่งเสริมการนำมาใช้ใหม่ ในการคืนสินค้าที่ใช้นแล้ว ให้ส่งกลับหรือ ติดต่อร้านค้าที่ลูกค้าซื้อมา ร้านค้าจะนำไปกำจัด หรือ นำไปรีไซเคิลอย่างถูกต้องเอง