



CitySwan LED gen3  
BPS/BRS/BWS 639  
Brand: Philips, Signify

<b>Scan me!</b> <b>DOWNLOAD</b>  	 	<b>Scan me!</b> <b>DOWNLOAD</b> <b>Service tag</b> 
--	------	--


220V 240V	outdoor 	CE	50Hz 60Hz	IP66	IK08	Max. 25°C Min. -40°C					
--------------	-------------	----	--------------	------	------	-------------------------	--	--	--	--	--




Led Colour		722	727	730	740	830
Light Source Energy Efficiency Class	Ledgine-O (4S)	E	E	D	D	E

Driver	Full Prog Driver			System Ready Driver			Connected Ready Driver		
	MCB	Qty	Inrush current	MCB	Qty	Inrush current	MCB	Qty	Inrush current
<i>Wattage/window</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>
40W (0,2-0,7)A S175	B 16A	30	18A/240μs	B 16A	-	-	B 16A	-	-
40W (0,2-1,0)A C123		-	-		30	24,6A/159,5μs		30	35,4A/122μs
110W (0,2-0,7)A C133		10	47A/250μs		-	-		-	-
110W (0,2-1,0)A C150		-	-		29	49A/290μs		11	71,9A/143μs


Luminaire	Dimensions (in mm)	m <sup>2</sup>	SCx (m <sup>2</sup> )	kg +/-5%
BPS 639	All dimensional drawings page 2	0,08		7,1
BRS 639		0,08		6,4
BWS 639		0,08		5,3




CitySwan LED gen3 BPS639  
Posttop  $\phi 60\text{mm}$





CitySwan LED gen3 BRS639  
Side entry  $\phi 48\text{mm}$





CitySwan LED gen3 BRS639  
Side entry  $\phi 60\text{mm}$





CitySwan LED gen3 BWS639  
Top side entry 3/4" thread






CitySwan LED gen3 BRS639  
Side entry  $\varnothing 48\text{mm}$





3 x2




2b

CitySwan LED gen3 BRS639  
Side entry  $\varnothing 60\text{mm}$




3 x2



2c


CitySwan LED gen3 BWS639  
Top side entry 3/4" thread



Dedicated CitySwan wall bracket  
To be ordred seperately  
Internal thread: 3/4" cylindrical  
pipe thread, min 40mm




2d

SR








5



IACZ node



6




7

8


9

x3



10

x4





© 2021-2025 Signify Holding

All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify Holding  
The Netherlands