







Cph gen2 LED and City
 BXS562/762
 Brand: Philips, Signify

Scan me!
DOWNLOAD







Scan me!
DOWNLOAD


Service tag



220V
240V

outdoor







50Hz
60Hz


IP66


IK07


Max.
25°C
Min.
-40°C

















--	--

Led Colour		722	727	730	740	830
Light Source Energy Efficiency Class	Ledgine-O (4S)	E	E	D	D	E


Driver	Full Prog Driver			System Ready Driver		
	MCB	Qty	Inrush current	MCB	Qty	Inrush current
<i>Wattage/window</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>
75W (0,2-0,7)A S240	B 16A	11	55A/200μs	B 16A	-	-
75W (0,2-0,7)A S240		-	-		8	67A/210μs
150W (0,2-0,7)A S240		10	47A/250μs		-	-
150W (0,2-0,7)A S240		-	-		15	11,2A/135μs

Luminaire	Dimensions (in mm)	 m ²	 SCx (m ²)	 kg +/-5%
BDS/BRS/BSS 562	All dimensional drawings page 2	0,12		8
BDS/BRS/BSS 762		0,12		8




583 - 440812001660
 2026-01-07
 © Signify Holding
 All rights reserved


Cph LED/City gen3 BRS562/762
Side entry ø48mm




Cph LED/City gen2 BRS562/762
Side entry ø60mm





Cph LED/City gen2
BDS562/762
Center 3/4" thread






Cph LED/City gen2
BSS562/762
Suspended/wire







6-8m







1

Cph LED gen2 BRS562
Cph City gen2 BRS762
Side entry $\varnothing 48\text{mm}$




2a

Cph LED gen2 BRS562
 Cph City gen2 BRS762
 Side entry $\varnothing 60\text{mm}$






2b

Cph LED gen2 BDS562
 Cph City gen2 BDS762
 Top entry 3/4" Pipe thread






2c

Cph LED gen2 BSS562
 Cph City gen2 BSS762
 Suspended/wire




2d


SR



SR to IACZ





5




IACZ node

6




7




8

9 x4



10 x4





© 2021-2025 Signify Holding

All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify Holding
The Netherlands