



Cph gen2 LED and City
BXS563/763
Brand: Philips, Signify

Scan me! DOWNLOAD 	 	 	Scan me! DOWNLOAD Service tag
--	----------	------	--

220V 240V	outdoor 	CE	50Hz 60Hz	IP66	IK08	Max. 25°C Min. -40°C					
--------------	-------------	----	--------------	------	------	-------------------------	--	--	--	--	--

--	--	--	--	--	--


Led Colour		722	727	730	740	830
Light Source Energy Efficiency Class	Ledgine-O (4S)	E	E	D	D	E

Driver	Full Prog Driver			System Ready Driver		
	MCB	Qty	Inrush current	MCB	Qty	Inrush current
<i>Wattage/window</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>	<i>type</i>	<i>qty</i>	<i>A/μs</i>
75W (0,2-0,7)A S240	B 16A	11	55A/200μs	B 16A	-	-
75W (0,2-0,7)A S240		-	-		8	67A/210μs
150W (0,2-0,7)A S240		10	47A/250μs		-	-
150W (0,2-0,7)A S240		-	-		15	11,2A/135μs


Luminaire	Dimensions (in mm)	m ²	SCx (m ²)	kg +/-5%
BDS/BRS/BSS 563/763 <120 LEDs	All dimensional drawings page 2	0,18		12
BDS/BRS/BSS 563/763 ≥120 LEDs		0,18		13,5









Cph LED/City gen2 BRS563/763
Side entry $\phi 60\text{mm}$






Cph LED/City gen2 BDS563/763
Center 3/4" thread





Cph LED/City gen2 BSS563/763
Suspended/wire






1

Cph LED gen2 BRS563
 Cph City gen2 BRS763
 Side entry $\varnothing 60\text{mm}$






2a

Cph LED gen2 BDS563
 Cph City gen2 BDS763
 Top entry 3/4" Pipe thread






2b

Cph LED gen2 BSS563
 Cph City gen2 BSS763
 Suspended/wire






2c


SR



SR to IACZ







5



IACZ node

6





7

8




9

x6



10

x6





© 2021-2025 Signify Holding

All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify Holding
The Netherlands