



GrandeVille LED

BPS962

Brand: Philips, Signify

Scan me!
DOWNLOAD

Scan me!
DOWNLOAD

Service tag

outdoor

220V
240V

50Hz
60Hz

IP65

IK10




Max. 25°C
Min. -40°C

3-5m


Led Color	LED Platform			830	840	CE
Light Source Energy Efficiency Class	CoB 1208			D	D	

Driver	Full Prog driver			System Ready driver			Connected Ready driver		
	MCB	Qty	Inrush current	MCB	Qty	Inrush current	MCB	Qty	Inrush current
40W (0,2-1,0)A	B 16A	30	18A/280µs						

Luminaire	Dimensions (in mm)								→ m ²	→ SCx (m ²)	⚠ kg +/-5%
	A	B	C	D	E	F	G	H			
BPS962	-	-	-	-	-	-	-	-	0,1000		7







Luminaire	Spigot/pole	H
BPS962	10Nm (M8)	3-5 M








1




583-440812001624
2026-01-06
© Signify Holding
All rights reserved





1



2



3



4



© 2021-2025 Signify Holding

All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify Holding
The Netherlands