


# Signify




Metropole LED gen2

BPS430


Brand: Philips, Signify

Scan me!  
DOWNLOAD




Scan me!  
DOWNLOAD




outdoor



220V  
240V

50Hz  
60Hz





IP66


IK10  
IK09\*


Max.  
25°C  
Min.  
-40°C


3-5m















Led Color	LED Platform	822	827	830	840	* SR Version IK09	
Light Source Energy Efficiency Class	CoB 1812	E	E	E	E		

Driver	Full Prog driver			System Ready driver			Connected Ready driver		
	MCB	Qty	Inrush current	MCB	Qty	Inrush current	MCB	Qty	Inrush current
40W (0,2-0,7)A	B 16A	30	18A/280µs	B 16A	-	-	B 16A	-	-
40W(0,2-1,0)A					30	24,6A/159,5µs		30	35,4A/122µs

Luminaire	Dimensions (in mm)								→ m <sup>2</sup>	→ SCx (m <sup>2</sup> )	→ kg +/-5%
	A	B	C	D	E	F	G	H			
BPS430	-	-	-	-	-	-	-	-	0,1600	0,0590	6,3-8






Luminaire	Spigot/pole	H
BPS430	12Nm (M8)	3-5 M



1



583-440812001710  
2025-12-12  
© Signify Holding  
All rights reserved




2




3

SHEILD  
OPTION



4



5



© 2021-2025 Signify Holding

All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

Signify Holding  
The Netherlands