


GreenUp Surface Mount


SM303C/SP303P/SM304C LED Downlight/筒射灯

Mounting instructions/安装说明书



Modular Type 型号	CRI 显色指数	CCT 色温	Beam Angle 光束角	Input 输入 220-240V,50/60Hz	Lum Dim. 灯具尺寸 Ø*H/L*W*H(mm)	Weight(kg) 重量
SM303C P6 PSU	≥80 / ≥90	2700K 3000K 3500K 4000K 5000K	NB MB WB VWB	0.06A,6W	Ø65*H126	0.353
SM303C P9 PSU	≥80 / ≥90			0.09A,9W	Ø65*H126	0.353
SM303C P6S PSU	≥80 / ≥90			0.06A,6W	L65*W65*H126	0.401
SM303C P9S PSU	≥80 / ≥90			0.09A,9W	L65*W65*H126	0.401
SP303P P6 PSU	≥80 / ≥90			0.06A,6W	Ø65*H256(吊线长度1500)	0.815
SP303P P9 PSU	≥80 / ≥90			0.09A,9W	Ø65*H256(吊线长度1500)	0.815
SP303P P6S PSU	≥80 / ≥90			0.06A,6W	L65*W65*H256(吊线长度1500)	0.905
SP303P P9S PSU	≥80 / ≥90			0.09A,9W	L65*W65*H256(吊线长度1500)	0.905
SM303C P20 PSU	≥80 / ≥90			0.11A,20W	Ø135*H193	1.4
SM303C P24 PSU	≥80 / ≥90			0.13A,24W	Ø160*H220	2.05
SM303C P28 PSU	≥80 / ≥90			0.15A,28W	Ø160*H220	2.05
SM304C P10 PSU	≥80 / ≥90		MB WB	0.10A,10W	Ø95*H100	0.485
SM304C P12 PSU	≥80 / ≥90			0.12A,12W	Ø95*H100	0.485
SM304C P15 PSU	≥80 / ≥90			0.15A,15W	Ø95*H100	0.485

Dimension 组件尺寸




Signify Luminaires (Shanghai) Co., Ltd.
Address: 2F, Building 1, No. 2555 Hechuan Road, Minhang District, Shanghai, P.R. China
Postalcode: 200233
斯诺飞灯具（上海）有限公司
地址：上海市闵行区合川路2555号1幢二楼
邮编：200233

Data subject to change without notice


PHILIPS

Philips and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V.


Suggested wire gauge 建议电源线规格




60227 IEC52 2x0.75 mm²
L: Brown/ 棕. N: Blue/蓝.



SM303C



SM304C



SM303P

