

Day-Brite

CFI

by  Signify

Recessed

SBP

Selectable backlit panel



Make the easy selection

Day-Brite /CFI Selectable backlit panel makes it easy for you to provide just the right product to your customers, at the right price.



Lumen Select Switch



CCT with Select Switch



UN3
Universal
120-347V


With 3 color temperature selections, 3 wattage choices, and 3 sizes available, you can provide numerous options to your customers, while keeping inventory levels and SKU count low. Available for use in recessed and surface mount applications, the SBP is a versatile luminaire that is ideal for general lighting applications.



SBP Selectable backlit panel

Carry less stock with more options

- Wattage and CCT are selectable via DIP switch on back of luminaire.
- Overall 1-1/2" deep luminaire, including driver box, provides minimal intrusion into the plenum space.
- Even distribution of light on the lens provides exceptionally low glare gradient minimizing distractions at the ceiling plane.
- General light distribution creates uniform horizontal and vertical illuminance on the workplane and limits scalloping on the walls.
- Excellent consistency of correlated color temperature (CCT) per ANSI C78.377.
- CRI 80 minimum color rendering with balanced spectrum.



Catalog Code	Size	Voltage	Power / Wattage			Lumens			Efficacy		
			3500K	4000K	5000K	3500K	4000K	5000K	3500K	4000K	5000K
1SBP2440L8CSP-4-UN3-DIM	1x4'	Universal 120-347	20	19	19	2590	2620	2624	131	137	134
			25	24	25	3228	3261	3261	128	131	131
			31	30	31	3902	3927	3906	124	129	125
2SBP2440L8CSP-2-UN3-DIM	2x2'	Universal 120-347	19	19	19	2584	2595	2607	134	121	134
			25	24	25	3389	3448	3463	136	141	139
			31	30	31	4015	4121	4030	128	135	129
2SBP4060L8CSP-4-UN3-DIM	2x4'	Universal 120-347	31	30	31	4356	4343	4419	139	141	140
			39	39	39	5433	5451	5468	136	140	138
			47	46	47	6332	6541	6454	133	141	136



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600,
Bridgewater, NJ 08807
Telephone 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.