

1 2 3 4 5 6 7 8 9 10

A

B

C

D

E

F





G

H

PHILIPS



Philips Lighting Electronics (Shanghai) Co., Ltd.
All rights are reserved. Reproduction in whole or in part is
prohibited without the written consent of the copyright owner.



Specification item	Value	Unit
Length (A1)	210.0 (+/- 0.3)	mm
Mounting hole distance (A2)	198.5 (+/-0.3)	mm
Width (B1)	30.0 (+/-0.5)	mm
Height (C1)	21.0 (+/-0.5)	mm
Mounting hole diameter (D1)	4.1 (+/-0.2)	mm
Mounting hole diameter (D2)	4.1 (+/-0.2)	mm

GB/T 1804-2000m (Unit: mm)																			
SIZE RANGE		0.5-3		>3-6		>6-30		>30-120		>120-400		>400-1000							
TOLERANCE		±0.1		±0.1		±0.2		±0.3		±0.5		±0.8		ITEM					
GENERAL ROUGHNESS		UNIT		MATERIAL										ASSEMBLY NO.		QUANT.			
✓		mm												MODEL NAME		CertaDrive ISO low ripple			
SCALE		PROJECT TYPE		TREATMENT										ORDER NO.		QUANT.			
				TITLE: Xitanium 18W 0.2-0.35A 51V DS 230V										PART NUMBER: 929003412000		2022-03-14 A			
																2022-05-25 B			
REV		CHANGE NO.		DATE															
DESIGNED BY		Yapeng.Lin				CHECKED BY				1		SH.		SH. 110 of 1		FORM NO.		A3	
DRAWN BY		Yapeng.Lin				APPROVED BY				REVISED BY				PHILIPS LIGHTING ELECTRONICS (SHANGHAI) CO., LTD					