

1 2 3 4 5 6 7 8 9 10

signify

A

B

C





D

E

F

G

H




Item	Dimensions
A1	125.0 +/-0.3
A2	109.0 +/-0.15
B1	45.0 +/-0.3
B2	30.0 +/-0.15
C	31.8 +/-0.3
D1	3.5 +/-0.15
D2	3.5 +/-0.15



GB/T 1804-2000m (Unit: mm)									
SIZE RANGE	0.5-3	>3-6	>6-30	>30-120	>120-400	>400-1000			
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8	ITEM	ASSEMBLY NO.	QUANT.
GENERAL ROUGHNESS	UNIT	MATERIAL							MODEL NAME
✓	mm								CertaDrive G4 48W
SCALE	PROJECT TYPE	TREATMENT							ORDER NO.
									QUANT.
		TITLE:							2023-05-30 A
		CertaDrive 48W 1.2A 40V 230V I							
		PART NUMBER:							
		92900 342 0780							
REV	CHANGE NO.	DATE							
DESIGNED BY	Yapeng.Lin			CHECKED BY	1 SH.			SH. 110 of 1	FORM NO.
DRAWN BY	Yapeng.Lin			APPROVED BY	REVISED BY			SIGNIFY (CHINA) INVESTMENT CO., LTD.	

1 2 3 4 5 6 7 8 9 10



Signify (China) Investment Co., Ltd.
All rights are reserved. Reproduction in whole or in part is
prohibited without the written consent of the copyright owner.

LED+
LED-