

PHILIPS

TrueCircle

Lighting

TrueCircle

Experience versatile
and functional modern
illumination

lighting.philips.com/truecircle



Contents

Introduction	2
Range overview	3
Product benefits	4
Product features	5
Application area	6
Dimensional drawings	7
Ordering codes	8

Introduction

TrueCircle is the perfect solution for your next office renovation project.

The combination of versatility, functionality and aesthetic appeal makes TrueCircle a popular choice for today's contemporary office interiors.

Available in recessed, surface and suspended versions, TrueCircle round luminaires provide installation flexibility. A sustainable, energy-efficient solution, they're designed to enhance office spaces like reception and main areas, corridors and hallways.



Range overview

- Available in circular shaped diameters of 380 mm and 500 mm
- Recessed, surface and suspended mounting options
- PSU and PSD drivers
- Color temperatures of 3000 K and 4000 K
- Opal and PSP (Prismatic) optics
- Black and white color options
- Energy-efficient LED technology
- Long lifetime of up to 50,000 hours at L80



Product benefits




Sustainable solution



Flexible, easy installation



Available in surface,
recessed and suspended
mounting options



Clean, simple design that
complements diverse
décor styles



Long-lasting,
high-quality
lighting



Black and white
color options

Product features


TrueCircle

round luminaires are the perfect solution for modern office renovations.

- Fluz- 2000lm & 3700lm
- 22W/38W
- Electrical class I
(Constant current, Class I)
- IP rating IP20

Available in:

- Sizes 380 mm and 500 mm
- PSU and PSD drivers
- Color temperatures of 3000 K and 4000 K at CRI 80



Versatile, functional modern illumination




Application area


The clean, simple design of TrueCircle round luminaires ensure they complement a variety of décor styles. With their distinct, sleek appearance, they add an element of style to any contemporary office space.

Available in recessed, suspended and surface options, their smooth curves are perfect when suspended in a cluster in a main reception area, or when spaced appropriately in larger areas such as corridors or hallways. Distributing light evenly in all directions, TrueCircle creates soft, diffused light that reduces glare, providing a comfortable environment for all employees.

Polar intensity diagrams




Recessed




Surface

Dimensional drawings


TrueCircle Surface D500






TrueCircle Surface D380



TrueCircle Recessed D500



TrueCircle Recessed D380



Ordering codes

12NC	Designation	Mounting	Type	CCT	Optics	Driver	Color	Dimension
912401483456	RC250B 20S/840 PSU PSP D380 WH	Recessed	LED20	830	Prismatic	PSU	WH	38cm
912401483433	RC250B 20S/830 PSU PSP D380 WH	Recessed	LED20	840	Prismatic	PSU	WH	38cm
912401483434	RC250B 20S/840 PSD PSP D380 WH	Recessed	LED20	830	Prismatic	PSD	WH	38cm
912401483435	RC250B 20S/830 PSD PSP D380 WH	Recessed	LED20	840	Prismatic	PSD	WH	38cm
912401483436	RC250B 37S/840 PSU O D500 WH	Recessed	LED37	830	Opal	PSU	WH	50cm
912401483437	RC250B 37S/830 PSU O D500 WH	Recessed	LED37	840	Opal	PSU	WH	50cm
912401483438	RC250B 37S/840 PSD O D500 WH	Recessed	LED37	830	Opal	PSD	WH	50cm
912401483439	RC250B 37S/830 PSD O D500 WH	Recessed	LED37	840	Opal	PSD	WH	50cm
912401483440	SM250C 20S/840 PSU PSP D380 WH	Surface	LED20	830	Prismatic	PSU	WH	38cm
912401483441	SM250C 20S/840 PSU PSP D380 BK	Surface	LED20	830	Prismatic	PSU	BK	38cm
912401483442	SM250C 20S/830 PSU PSP D380 WH	Surface	LED20	840	Prismatic	PSU	WH	38cm
912401483443	SM250C 20S/830 PSU PSP D380 BK	Surface	LED20	840	Prismatic	PSU	BK	38cm
912401483444	SM250C 20S/840 PSD PSP D380 WH	Surface	LED20	830	Prismatic	PSD	WH	38cm
912401483445	SM250C 20S/840 PSD PSP D380 BK	Surface	LED20	830	Prismatic	PSD	BK	38cm
912401483446	SM250C 20S/830 PSD PSP D380 WH	Surface	LED20	840	Prismatic	PSD	WH	38cm
912401483447	SM250C 20S/830 PSD PSP D380 BK	Surface	LED20	840	Prismatic	PSD	BK	38cm
912401483448	SM250C 37S/840 PSU O D500 WH	Surface	LED37	830	Opal	PSU	WH	50cm
912401483449	SM250C 37S/840 PSU O D500 BK	Surface	LED37	830	Opal	PSU	BK	50cm
912401483450	SM250C 37S/830 PSU O D500 WH	Surface	LED37	840	Opal	PSU	WH	50cm
912401483451	SM250C 37S/830 PSU O D500 BK	Surface	LED37	840	Opal	PSU	BK	50cm
912401483452	SM250C 37S/840 PSD O D500 WH	Surface	LED37	830	Opal	PSD	WH	50cm
912401483453	SM250C 37S/840 PSD O D500 BK	Surface	LED37	830	Opal	PSD	BK	50cm
912401483454	SM250C 37S/830 PSD O D500 WH	Surface	LED37	840	Opal	PSD	WH	50cm
912401483455	SM250C 37S/830 PSD O D500 BK	Surface	LED37	840	Opal	PSD	BK	50cm
Suspention set								
912401483461	SP250Z SM3							
Power cables(Silver) with colored ceiling caps								
910505103765	SP250Z C1700P3 WH							
910505103766	SP250Z C1700P3 BK							
910505103767	SP250Z C1700P5 WH							
910505103768	SP250Z C1700P5 WH							



Signify, previously known as Philips Lighting, is the world leader in connected LED lighting systems, software and services. We proudly market the best lighting brands in the world, including Philips and Interact.

PHILIPS

The Philips brand stands for quality and energy-efficiency in light. For over 125 years, Philips products have been at the forefront of innovation. Today Philips is recognized as the leading brand in lighting.

interact

Interact is a portfolio of IoT-enabled software suites that manage connected lighting systems and the data that those systems collect. Interact software manages, monitors, and controls lighting systems that include connected luminaires, sensors, and other connected devices from Signify and third-party manufacturers.

You and Signify – a reliable partnership

Close cooperation before, during and after projects is important to us. Our loyal service teams are committed to ensuring you receive both competent support and any information you require.

We work closely with local wholesalers to offer you flexible and on-time delivery, with product availability you can rely on to help you stay on top. Plus the **Signify Lighting Academy** provides you with a comprehensive range of educational resources for you to grow your expertise and get certified.

[signify.com/specifiers](https://www.signify.com/specifiers)

Brighter lives, better world

Signify has been 100% carbon neutral since September 2020.

We recycle up to 90% of our manufacturing waste.

We use 100% renewable electricity.

Our paper packaging for LED lamps and luminaires is saving over 500,000 kilos of plastic waste per year.

Thank you for choosing Philips products, offered by Signify, and joining us on our mission.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

lighting.philips.com