

WingLine

RC480B 2x2

Mounting Instruction

4415 109 24720




IEC
EN60598



IP20




t_a 45°C



Type	Dimension L x W X H (mm)	Kg
RC480B W60L60	595 x 595 x 75	4.0



Diffuser





Note : Actual product may differ from pictorial view.


Supply Connection

Connect the supply cable in terminal block,

NOTE: DO NOT OPEN ANY OTHER SCREWS
(open only Connector screws)




FOR PSU SERIES



Insert 3 wires L, N, & E in 3 Pin Terminal connector.

FOR PSD SERIES





Insert 3 wires L, N, & E in 3 Pin Terminal connector.

Insert 2 wires for Dali+ & Dali- in 2 Pin terminal connector

Recessed Mounting


1




Engage safety chains in hook

NOTE:- Safety chain not included in product.
Customer need to buy separately.

2




Push the Luminaire inside ceiling Structure after connections (Push the driver side first)



Put luminaire gently on the T-section of ceiling structure

Luminaire is ready for operation.

3



1. For Indoor use only.
2. The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
3. Do not switch on before completing the installation.
4. The luminaire shall, under no circumstance, be covered with insulation matting or similar material.
5. The luminaire is not suitable for direct mounting on normally flammable material.
6. The corrosive atmosphere or hazardous material such as sulphur, chlorine, phthalate etc must be avoided during the use & storage.

PHILIPS