

Day-Brite

CFI

by  Signify

Recessed

FluxGrid gen 2



Finally, a troffer tailored to your needs

Who says that you can't have aesthetics, high performance, DLC Standard and Premium listed lumen packages, and multiple color temperatures, all within budget?

Day-Brite / CFI FluxGrid gen 2 troffer is setting a new standard that delivers it all without extra costs.

Value, options, and service

Day-Brite / CFI has expanded its FluxGrid family with the development of FluxGrid gen 2. Designed to check all of your key "must haves" off the list, FluxGrid gen 2 covers all of your needs from performance and ROI, to budget, specifications, or shipping requirements.

Looking for maximum savings and utility rebates? Choose one of the 42 standard and base options which are DLC Standard or Premium (see back cover for details).

Looking to lock up a spec with other specific criteria or to take advantage of the latest controls? Mix and match the various options to find just what you want.



FluxGrid gen 2 at a glance:

- 1x4, 2x2, and 2x4 models
- 1500 to 9000 lumens
- CCT 3000-5000K, 80 CRI or 3500-5000K, 90 CRI
- DLC premium and standard models available*
- Round or flat diffuse lens options
- All drivers and boards are easily accessible from below
- Air return function available
- Integral emergency options
- Interact ready wireless sensor options
- Compatible with many industry control partners and protocols such as 0-10V, DALI, and bluetooth



Air Return




Sensor



Diffuse round lens



Diffuse flat lens



Key takeaways

- All models are attractive and easy to install/maintain
- Can be stock ready (ships in 2 days) or design ready (ships in 5-10 days)
- High performance and rebate potential
- Various integral control options
- A product family you can configure to fit your exact needs

* Not all product variations listed are DLC qualified. To ensure that a specific model is qualified, visit www.designlights.org/search



interact
ready.

FluxGrid gen 2

The right selection of service, features and value made easy

Flexibility and ROI driven: Performance without compromise									
Luminaire	Catalog Number	Input Power	80 CRI Efficacy	Estimated 90 CRI Efficacy	Buy America Option ²	DLC Premium ¹	DLC Standard ¹	1% Dimming	10% Dimming
1x4 Standard	1FGXG15L840-4-RS-UNV	10	146	139	✓	✓		✓	
	1FGXG30L840-4-RS-UNV	21	143	136	✓	✓		✓	
	1FGXG38L840-4-RS-UNV	27	140	133	✓	✓		✓	
	1FGXG45L840-4-RS-UNV	34	137	130	✓	✓		✓	
	1FGXG54L840-4-RS-UNV	41	133	126	✓	✓		✓	
2x2 Standard	2FGXG15L840-2-RS-UNV	11	141	134	✓	✓		✓	
	2FGXG20L840-2-RS-UNV	14	142	135	✓	✓		✓	
	2FGXG30L840-2-RS-UNV	22	139	133	✓	✓		✓	
	2FGXG38L840-2-RS-UNV	28	136	129	✓	✓		✓	
	2FGXG45L840-2-RS-UNV	34	133	126	✓	✓		✓	
	2FGXG54L840-2-RS-UNV	43	128	121	✓	80CRI	90CRI	✓	
	2FGXG60L840-2-RS-UNV	47	125	119	✓	80CRI	90CRI	✓	
2x4 Standard	2FGXG20L840-4-RS-UNV	14	146	139	✓	✓		✓	
	2FGXG38L840-4-RS-UNV	27	141	134	✓	✓		✓	
	2FGXG43L840-4-RS-UNV	31	139	132	✓	✓		✓	
	2FGXG48L840-4-RS-UNV	36	137	130	✓	✓		✓	
	2FGXG54L840-4-RS-UNV	41	134	128	✓	✓		✓	
	2FGXG74L840-4-RS-UNV	60	125	119	✓		✓	✓	
	2FGXG85L840-4-RS-UNV	63	136	129	✓		✓	✓	
	2FGXG90L840-4-RS-UNV	67	135	128	✓		✓	✓	

Budget driven: Tailored configurations and lowest price									
Luminaire	Catalog Number	Input Power	80 CRI Efficacy	Estimated 90 CRI Efficacy	Buy America Option ²	DLC Premium ¹	DLC Standard ¹	1% Dimming	10% Dimming
1x4 Base	1FGXG42B840-4-RS-UNV	30	139	133	✓	✓			✓
2x2 Base	2FGXG38B840-2-RS-UNV	32	120	114	✓	80CRI	90CRI		✓
2x4 Base	2FGXG42B840-4-RS-UNV	30	141	134	✓	✓			✓

1 Not all product variations listed on this page are DLC qualified. To ensure that a specific model is qualified, visit www.designlights.org/search
 2 Failure to properly select the "BAC" suffix could result in you receiving product that is not BAA compliant product with no recourse for an RMA or refund. This BAC designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Consult Signify to confirm whether specific accessories are BAA-compliant.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
 200 Franklin Square Drive,
 Somerset, NJ 08873
 Telephone 855-486-2216

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.