



Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Ordering guide

Example: BU1 A

Product Code	Finish	
BU1		
BU1 Composite Bullyte	A	Black
	H	Bronze
	G	Verde

*1 US and CAN: 50 Watt PAR 20, HID/INC.
 *2 Shroud Sold Separately.

Specifications

Housing

Fully rotatable shroud, gasketed, ULTEM® High Performance Polymer composite. One-piece injection molded ULTEM® High Performance Polymer composite. Fully-adjustable swivel arm with vibration-proof locking teeth. Gasketing is silicone. Fasteners are 300 series stainless steel. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

Finish

Composite is textured, pressure formed, molded-in-color.

Optical Assembly

Provided with optional shrouds only.

Lamping

50 Watt Maximum HID. 50W maximum PAR20/R20 medium base lamp. (USA) 35W maximum PAR20/R20 medium base lamp. (CANADA) Lamp is not included. Lower wattage lamps are acceptable. (Note: If HID or R lamp is used, accessory shroud must also be used.)

Electrical Assembly

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

Ballast

Must order inground (IBH) or above ground (ABH) ballast housing separately.

Warranty

Ten-year limited warranty.

Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width

3 7/8" (98mm)

Length

8 1/2" (216mm)

Max. Weight

.95 lb.

