

LIGHTOLIER

by  Signify

Downlighting

Calculite LED

SL Shower light trim



Experience the change, see the difference... again, and again

Architectural showerlight provides the right illumination and the safety you need in wet locations.

Benefits

Calculite's showerlight is not just a modification to the downlight product, it was purposefully designed with wet locations in mind. The non-conductive flush mount lens with pre-installed gasket takes the worry out of wet location safety. It also reflects the lustrous architectural look and lighting performance that you've come to expect in all of the Calculite generation 3 downlights.



SL Calculite LED

Shower light trim downlighting



Features

Apertures: 4" & 6" round

Finish: Matte white flange with diffuse lens

Reflectors: Specify white (WH) reflector finish. Must use flangeless trim option

Lumens: 4" in 500–3000lm; 6" in 1000–6000lm

Construction: Flush mount non-conductive lens with pre-installed gasket

Installation: One-piece reflector and lens allows for similar installation as standard trims*

Labels: cULus wet location

Warranty: 5 year

Frame Complete luminaire = Frame + Engine + Trim

example: **4RNLC**

Series	Installation	Options
4R Calculite LED 4" Round	N New construction (Non-IC)	– Universal 120/277V (specify for POE)
6R Calculite LED 6" Round	R Remodeler (Non-IC)	LC Chicago Plenum EM Emergency
	A AirSeal (IC)	– N/A

3 347V
3RADIO 347V Integral Interact Pro RF sensor (enables wireless connected lighting control)
RADIO Integral Interact Pro RF sensor (enables wireless connected lighting control)

Engine

example: **C4L15835NZ10U**

Series	Lumens	CRI	CCT	Beam	Dimming	Voltage
C4L Calculite LED 4"	05 500lm	8 80CRI 9 90CRI	27 2700K 30 3000K 35 3500K 40 4000K	N Narrow M Medium W Wide	Z10 0–10V 1% D Dali L Lutron EcoSystem (Other controls options available, see specification sheets for details.)	U Universal (120/277/347V)
	10 1000lm					
	15 1500lm					
C6L Calculite LED 6"	10 1000lm	35 3500lm 48 4800lm 60 6000lm 25 2500lm				
	15 1500lm					
	20 2000lm					
	25 2500lm					

Trim

example: **C4RSLWH**

Series	Style	Finish
C4R Calculite LED 4" Round	SL Shower light trim (non-conductive)	WH White (matte)
C6R Calculite LED 6" Round		

Note: Prior to ordering, consult specification sheets for the most current information, notes, and exclusions.

* Wet location rated shower light is applicable in any installation requiring dead front trims, interior or exterior non-corrosive applications, or where a diffused lens at the ceiling is required.



Visit [Signify.com/warranties](https://www.signify.com/warranties) for more information on Signify's standard 5-year limited warranty.

See specification sheet C4RDL or C6RDL for additional drawings and technical information.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.