

4" x 3"
Tapered

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Order guide

example: P1526 8 A T D

Product Code	Pole Height	Finish	Outlet Location	Outlet Options
P1526				
P1526	8' 10' 12' 14'	A Black B White G Verde H Bronze J Green	T 12" Down from Top - Aligned with House Side B 4" Up from Top of Base - Aligned with House Side	D Standard Duplex G GFI Duplex

Note: Top outlets not available with the HFP arms. EPA values based on destructive break testing. For AASHTO ratings, contact factory.

Pole Data

Pole Model	Pole Shape	Pole Type	Shaft Dimension	Pole Fluted	Anchor Base Shape	Bolt Circle	Base Dim (in)	Hand Hole Dim (in)
P1526	Round	Tapered	4 to 3	Smooth	square	9.375	8.25 x 27.375	3 x 5

Pole Family	Catalog Number	Nominal Height (ft)	Tenon Section (in)	Wall Thickness (in)	EPA Rating 80 MPH (sq. ft)	EPA Rating 100 MPH (sq. ft)	Anchor Bolts (in)
P1526	P1526-8	8	3	0.125	10.24	5.78	1/2-15 1/2 bs
P1526	P1526-10	10	3	0.125	8.12	4.44	1/2-15 1/2 bs
P1526	P1526-12	12	3	0.125	6.64	3.50	1/2-15 1/2 bs
P1526	P1526-14	14	3	0.125	7.57	4.26	1/2-15 1/2 bs

Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy. 319 Permanent mold aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:


Please visit www.signify.com/warranties for more details on structural and finish warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P1526 Poles and Brackets

Tapered Round Smooth



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

