



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: B3 A

Product Code	B3	Aluminum Bullyte
Finish	A H G	Black Bronze Verde

Specifications

HOUSING:

Die-cast aluminum. Fully-adjustable swivel arm with vibration-proof locking teeth. Gasketing is silicone. Fasteners are 300 series stainless steel. Fully rotatable shroud, gasketed, cast aluminum. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

FINISH:

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting.

OPTICAL ASSEMBLY:

Clear tempered glass affixed at 10° angle for natural cleaning.

LAMPING:

100W maximum PAR30/R30 medium base lamp. Lamp is not included. Lower wattage lamps are acceptable. HID PAR30 MH or MV acceptable with remote ballast (not included).

ELECTRICAL ASSEMBLY:

4kv rated porcelain mini-can base. Nickel-plated screw shell with center contact.

BALLAST:

Must order inground (IBH) or above ground (ABH) ballast housing separately.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Width: 5 5/16" (135mm) **Length:** 9 1/2" (241mm) **Max. Weight:** 2.96 lb.

