

CHLORIDE

by  Signify

Exit/Emergency

SX series

LED die-formed steel exit sign
NYC Approved 8" letters



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Example: SXLRW

- SXLRW** Exit – AC Only, Red, LED, Universal, White housing with white face
SXLRWEM Exit – Nicad battery, Red, LED, Universal, White housing with white face

Accessories

WG4 – Wire Guard

Note :

For black housing change the "W" to a "B" in above catalog number .

codes and standards

- UL listed to Standard 924
- NFPA 101 (Life Safety Code)
- NFPA 70 (National Electric Code)
- New York City Approved (8" letters)
- UL listed for damp location

construction

- Rugged 20 gauge steel construction .
- Field selectable chevrons .
- Housing is finished in a white durable powder coat .
- Black housing available .

installation

- Universal mounting : wall , ceiling or end mount .
- Canopy is not required on wall mount .
- Exit signs are provided with an extra stencil face plate for double face applications .

electronics

- Isolated short circuit and voltage protection circuit .
- Test switch and LED indicator light .
- Low voltage disconnect feature prevents deep battery discharge .
- 24 hour recharge after 90 minute discharge .
- 120/277 VAC , Dual Voltage input .
- Power Consumption: 5W max .

LED

- Exit face illumination is provided by a special high intensity indirect red LED strip .
- Letter brightness and illumination uniformity exceed UL requirements .
- Uniform 8" letter illumination (1" stroke) .

battery

- UL recognized nickel cadmium battery in EM exit .
- Provides a minimum 90 minutes of emergency illumination while in the emergency mode .

warranty

- Five year warranty on exit



SX LED die-formed steel exit sign

NYC Approved 8" letters

dimensions

