


Frame-in Kit



Reflector Trim

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

Frame-In Kit	Reflector Trims — See Individual Reflector Trim Specification Sheets					
	Open Downlight			Adjustable	Enclosed Diffuser	Wall Washer
1100DAICM	Reflector	Baffles	Basic White	Eyeball		
	<b>1144</b> <b>1144CD</b> <b>1146</b> <b>1146CD</b>  Cone: <b>1113</b> <b>1113CD</b> <b>1113WH</b>	<b>1105</b> <b>1105WH</b> <b>1176</b> <b>1176WH</b>	<b>1171</b>	<b>1182</b>	<b>1124</b> <b>1126</b> <b>1128</b> <b>1177SH</b> <b>1178SH</b> <b>1190</b>	<b>1196</b>

# 1100DAICM Lytecaster INC 6 3/4"

## Deep AirSeal IC frame

### Features

- 1. Housing:** Walls .032" aluminum. Cover .026" galvanized steel. UL listed for direct contact with thermal insulation. AirSeal® housing minimizes air leakage to less than 2 CFM at 1.57 PSF, which complies with Model Energy Code (Section 602.3.3) and the Washington State Energy Code (Section 502.4) and reduces heat loss and condensation in ceiling. Access door for inspection of junction box.
- 2. Mounting Frame:** .036 (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. 3/8" deep integral lip. Four slots are positioned 90° apart to simplify alignment. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- 3. Junction Box:** 2" X 4" X 4"; .063" (#14 ga.) galvanized steel. UL listed for maximum of 6 No. 12 ga., 90° C through branch circuit conductors. Quick release "L" shaped cover for outside access to wiring. Access door inside of housing allows easy inspection of wiring without removal of housing. Integral cable clamps permit attachment of nonmetallic, Romex® without the need for additional connectors.
- 4. Mounting Bars:** .059" (#16 ga.) galvanized steel. Bars pivot for easy attachment and wire-in below ceiling line. Bars extend to accommodate 16" to 24" O.C. joist spacing and feature integral nail for secure attachment to wood construction. Attaches to T-bar ceilings without the need of accessories.
- 5. Socket Housing:** Galvanized steel.

**6. Socket:** Porcelain medium base; nickel plated screw shell.  
Pre-wired with #18 ga. SF1 leads to junction box.

**7. Thermal Protector:** Meets NEC and UL requirements. Located inside housing.

### Options & Accessories

**Extra-Thick Ceiling Mounting Ring:** **1967A** - up to 2" thick ceiling.

### Labels

UL Type I.C. (Suitable for Damp Locations);

Complies with Air Leakage Requirements as stated in the Model Energy Code, California Title 24 and the Washington State Energy Code.

AirSeal® is a registered trademark of Lightolier.

Romex® is a registered trademark of General Cable Industries Inc.



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.