



Project:	
Location:	
Cat.No:	
Type:	
Lamps:	Qty:
Notes:	

### Ordering guide

Example: DAL 1 A

Product Code	Finish
<b>DAL 1</b>	
DAL 1 Aluminum Deck Light	A Black H Bronze

- Each product will ship with an S7
- BAB Lamp is optional

### Specifications

#### Housing

Body and mounting plate are cast aluminum construction. Fasteners are 300 series stainless steel.

#### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications.

#### Optical Assembly

Frosted, annealed glass lens. Reflector is Stamped Hammer-tone Aluminum.

#### Lamping

10W maximum T3 bi-pin lamp. Lower wattage lamps are acceptable. 10W T3 lamp is included with the fixture.

#### Electrical Assembly

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 6-ft. pigtail of 18-2 AWG, 105° C, SPT-1W wire. 12 Volt system requires remote transformer, not included.

#### Installation & Mounting

Two (2) stainless #8 wood screws (supplied) via key slots.

#### Warranty

Three-year limited warranty.

#### Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 standards.

Height	Width	Depth	Max. Weight
3 1/2" (89mm)	3 1/2" (89mm)	1 7/8" (48mm)	0.30 lb

