

Vaya Tube RGB

Compact linear direct view luminaire for dynamic media & graphic effects

Date: _____
Type: _____
Firm Name: _____
Project: _____

Vaya Tube is a compact direct view linear LED lighting solution for exterior accent and low-resolution graphic lighting applications. Designed for media graphics with a resolution up to 150 mm, the DMX and KiNet-controllable system can transform entire facades with bright and uniform light, in either RGB or White/Mono color. The light-weight luminaire minimizes the loading onto structures and cladding elements, while run-lengths of up to 12 m (40 ft) per Control Module port (x2) allow for flexible wiring. Simple push'n'click connectors ensure a simple, fast and reliable installation.

- Slim & Light-Weight - The slim form factor, different length options and light-weight of the luminaire ease the integration into façade cladding elements and minimize excess loading onto architectural structures.
- Uniform & Bright—Create a uniform band of light in a wide 180 degree viewing angle, while ensuring high visibility with an output of 300 lm/68 cd per 1.2 m (4 ft)
- Contour & Content - Whether outlining the contour of a building, placing accents onto a façade or creating a media display of dynamic graphics, Vaya Tube places a variety of control options at your fingertips from static on/off setups to dynamic control in resolutions ranging from entire runs down to 150 mm (6 in) segments.



[Product page](#)

Beam Angle	165° x 110°
Lumens per foot*	72
Efficacy	20.4 to 21.8
LED Channels	Red/Green/Blue

Input Voltage	24 VDC
Weight	360 g (0.8 lb) for 1 ft 780 g (1.7 lb) for 4 ft
Housing Material	Extruded polycarbonate, dark grey
Approbations	UL/cUL, FCC Class A, CE, CQC, RCM
Environment	Dry/Damp/Wet Location, IP66
Applications	Direct View

Specification Sheets

Custom products information available

PDF Download	Beam Angle	Lumens*	Power	Weight	Item Number	12 NC
RGB, Ethernet & DMX, 0.3 m (1 ft) 150 mm (6 in) Pitch, UL, CE, CQC	165° x 110°	72	3.5 W	360 g (0.8 lb)	316-000014-02	912400130499
RGB, Ethernet & DMX, 1.2 m (4 ft) 150 mm (6 in) Pitch, UL, CE, CQC	165° x 110°	303	14 W	780 g (1.7 lb)	316-000014-03	912400130501

* Lumen output measurements comply with IES LM-79-08 testing procedures.

COLORKINETICS vayaseries

© 2020 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/vaya