

Vaya Flood HP RGB

High power architectural LED flood light for dynamic color-changing lighting effects

Date: _____
Type: _____
Firm Name: _____
Project: _____

Vaya Flood HP is a reliable and cost effective high output LED flood lighting solution ideal for illuminating large-scale exterior facades, bridges, and monuments. While minimizing initial investment, this Vaya Flood series provides exceptional flexibility to create eye-catching flood, wash and spot lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

- Powerful - Throwing light with 10x up to 94 m / 1fc up to 307 ft high, this narrow beam luminaire is a powerful solution for any size of project.
- Compact - Unlike other flood lighting solutions, the Vaya Flood series are compact sized & light-weight luminaires, that combine an aluminium die-cast housing which is both anodized and powder coated to protect against corrosion, tempered glass, pressure equalizing air vents and IP66 outdoor rating, making the product robust against harsh outdoor environments.



[Product page](#)

Beam Angle	10°, 20°, 40°
Lumens*	3,335 to 3,660
Efficacy	31.1 to 34.3
LED Channels	Red/Green/Blue

Input Voltage	100 to 277 VAC, 50/60 Hz
Power Consumption	105 W
Weight	7.5 kg (16.5 lb)
Housing Material	Die-cast aluminium, dark grey powder-coated finish
Approbations	UL/cUL, FCC Class A, CE, PSE, CQC, RCM
Environment	Dry/Damp/Wet Location, IP66
Applications	Flood Lighting, Spot Lighting, Wall Washing

Specification Sheets

PDF Download	Beam Angle	Lumens*	Item Number	12 NC
RGB, 10°, CQC/CE/PSE	10°	3,660	316-000009-00	910503702884
RGB, 10°, UL	10°	3,660	316-000009-03	910503702887
RGB, 20°, CQC/CE/PSE	20°	3,335	316-000009-01	910503702885

COLOR KINETICS
vaya series

Specification Sheets (cont.)

PDF Download	Beam Angle	Lumens*	Item Number	12 NC
RGB, 20°, UL	20°	3,335	316-000009-04	910503702888
RGB, 40°, CQC/CE/PSE	40°	3,401	316-000009-02	910503702886
RGB, 40°, UL	40°	3,401	316-000009-05	910503702889

* Lumen output measurements comply with IES LM-79-08 testing procedures.

COLORKINETICS vaya series

© 2019 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed.

Color Kinetics
www.colorkinetics.com/vaya