




DaySpace


Light as natural as daylight












Why it's easy to choose DaySpace

- Optical design and clean aesthetic result in soft light with low-glare.
- Excellent workplane uniformity with vertical and horizontal illumaination.
- Flexible choices of suspended and recessed mounting
- Customizable backplate for creative freedom
- Multiple lumen packages and three dierent standard color temperatures 4000K and 6500K.



Array of Patterns








Benefits





- Discreetly integrates into the ceiling
- Appear weightless
- Sleek and minimalist aesthetic

Applications





Offices Healthcare Schools





Drywall

Banks Hospitality Fashion

- On Site Articulation
- Endless array of patterns

Ceilling types



T-grid

- Customizable backplate
- For one-of-a-kind designs
- Gentle, glare free illumination
- Increased acoustics









DaySpace

Endless Possibilities, Create your own design

DaySpace is offered in suspended and recessed mounted. The luminire can be covered from the back side with the Armstrong ceiling that is being used in the ceiling or the metal back plates in selected RAL shaded available in the catalogue. Standard back plate templates are also available which the designers can customize on their own to integrate them with the interiors

Back Plate Option


Finished attachments which can be ordered from Philips



Standard Back Plate Template

Template which can be used at site by the Interior install






Accent Colors



Fabric



Back painted glass



Wood Grains



Technical Specification

S. No.	Description	RC740B (DaySpace)		
1	System Lumen	2500, 3000 & 3600 lumen		
2	ССТ	6500 K / 5700 K / 4000 K		
3	CRI	Greater than 80		
4	SDCM	<5		
5	Efficacy	>90 Lm/W		
6	Luminaire Depth	Maximum Luminaire Hight ~90mm		
7	Dimensions	595x595x 93 mm		
8	THD	<10 %		
9	PF	0.95		
10	Life	L70B50@ 50K Hrs.		
11	Driver	Fixed output / DALI		
12	Diffuser	Sigle Piece PC Diffuser		
13	Housing	CRCA		
14	Mounting Options	Recess		
15	Look and Feel	Diffused Luminaire		
16	Serviceability	Class B		

Ordering Data

S. No.	12 NC	Description	Qty Per Box
1	9195 158 12987	RC740B LED25S/865 W60L60 PSU WH	2
2	9195 158 12988	RC740B LED25S/857 W60L60 PSU WH	2
3	9195 158 12989	RC740B LED25S/840 W60L60 PSU WH	2
4	9195 158 12990	RC740B LED30S/865 W60L60 PSU WH	2
5	9195 158 12991	RC740B LED30S/857 W60L60 PSU WH	2
6	9195 158 12992	RC740B LED30S/840 W60L60 PSU WH	2
7	9195 158 12993	RC740B LED36S/865 W60L60 PSU WH	2
8	9195 158 12994	RC740B LED36S/857 W60L60 PSU WH	2
9	9195 158 12995	RC740B LED36S/840 W60L60 PSU WH	2
10	9915 158 13255	RC740B LED25S/865 W60L60 PSU WH	2
11	9195 158 13256	RC740B LED25S/857 W60L60 PSU WH	2
12	9195 158 13257	RC740B LED25S/840 W60L60 PSU WH	2
13	9195 158 13258	RC740B LED30S/865 W60L60 PSU WH	2
14	9195 158 13259	RC740B LED30S/857 W60L60 PSU WH	2
15	9195 158 13260	RC740B LED30S/840 W60L60 PSU WH	2
16	9195 158 13247	RC740B LED36S/865 W60L60 PSU WH	2
17	9195 158 13254	RC740B LED36S/857 W60L60 PSU WH	2
18	9195 158 13246	RC740B LED36S/840 W60L60 PSU WH	2

Dimensional Diagram

