

Poles & Brackets

Urban Decorative

P1150 Series Poles



Project:			
Location:			
Cat.No:			
Туре:			
Qty:			
Notes:			

Ordering guide

example: P1150 126 A

Product Code	Pole Height	Finish	Accessory Location	Pole Accessories	Tenon Options
P1150	 86 8ft, 6in 106 10ft, 6in 126 12ft, 6in 146 14ft, 6in 	 A Black B White G Verde H Bronze I Gray J Green Z Custom 1 	 N No Option T 12" Down from Top - Aligned with House Side B 4" Up from Top of Base - Aligned with House Side Z Custom 	 N No Option D Standard Duplex G GFI Duplex M Motion Control ¹ 	 N Standard Tenon - 3" OD x 3" ISF Internal Slip Fitter (for HFP Brackets) T4 4" OD Tenon or 4" pole w/o standard 3" tenon (consult factory for 3" poles)

Note: Top outlets not available with the HFP arms. Consult factory for HFP arm outlet mounting.

Hadco P1150 Series decorative aluminum poles provide a wide range of options in a timeless aesthetic. All poles are made in the USA and always open to a wide range of add-ons and customizations to meet any project need.

1. Consult factory for quotation.


Anchor Bolts & Templates (ordered separately)


12NC	Description
912400110296	ANCHOR BOLT, 1/2-13x15x3, 4/PK
912400128345	AB TEMPLATE, P1150

P1150 Series Urban Decorative Poles

Dimensions

10ft 6in model shown.





4.88" Dia. Area for Conduit

P1150 Series Poles 09/22 page 2 of 6

P1150 Series Urban Decorative Poles

Pole Specifications

Pole Family	Catalog Number	Pole Dia. (in.)	Pole Shape	Pole Style	Pole Height (ft.)	Wall Thickness (in.)	Tenon OD x H (in.)	Weight (Ibs.)	Bolt Circle (in.)	Base Size Dia. x H (in.)	Hand Hole Size W x H (in.)	Anchor Bolts (in.)
P1150	P1150-86	4-3	Tapered	Smooth	8.5	0.125	3 x 3	32	7	11 x 30	4.25 x 4.5	1/2 x 15 x 3 (4)
P1150	P1150-106	4-3	Tapered	Smooth	10.5	0.125	3 x 3	36	7	11 x 30	4.25 x 4.5	1/2 x 15 x 3 (4)
P1150	P1150-126	4-3	Tapered	Smooth	12.5	0.125	3 x 3	38	7	11 x 30	4.25 x 4.5	1/2 x 15 x 3 (4)
P1150	P1150-146	4-3	Tapered	Smooth	14.5	0.125	3 x 3	42	7	11 x 30	4.25 x 4.5	1/2 x 15 x 3 (4)

Tenon height is nominal, the available tenon height can be greater on tapered poles. Anchor bolt max projection is determined by the anchor bolt template.

EPA Data

Pole Family	Catalog Number	80 MPH	90 MPH	100 MPH	110 MPH	120 MPH	130 MPH	140 MPH	150 MPH
P1150	P1150-86	10.72	8.09	6.21	4.82	3.76	2.94	2.29	1.76
P1150	P1150-106	8.60	6.43	4.87	3.72	2.85	2.17	1.63	1.19
P1150	P1150-126	7.10	5.25	3.93	2.95	2.20	1.63	1.17	0.79
P1150	P1150-146	5.99	4.38	3.23	2.38	1.73	1.22	0.82	0.50

P1150 Series

Urban Decorative Poles

Hadco poles are available with a wide variety of decorative and functional add-ons, adapters, and accessories. Use in combination with Hadco Poles and Hadco Post Top and Hanging Arms to realize your project's vision.

example: M0012-A

Post To	op Tenon Adapter	example: M0090-A		
Product	Code	Finish		
M0090 M0091 M0093	4" round pole to 3" OD luminaire tenon 3" square pole to 3" OD luminaire tenon 4" square pole to 3" OD luminaire tenon	A Black B White G Verde H Bronze I Gray J Green Z Custom		



example: BA31A18B-A

Ladder Rest

Product	Finish	
M0012]	
M0012	For 3" OD Tenons (includes extended 3" OD top tenon)	A Black B White G Verde H Bronze I Gray J Green Z Custom



Banner Arm Bracket

Pro BA	duct Code	Pole Dia.	# of Arms	Materials A	Length	Finial B	Finish
BA	Banner Arm Bracket	3" 4" 5"	1 One 2 Two at 180°	A Aluminum	18" 24" 30"	B Ball	A Black B White G Verde H Bronze I Gray J Green Z Custom



Tie Down Bracket

example: TD32-H

Product Code TD	Pole Dia.	# of Arms	Finish
TD Tie Down Bracket	3" 4" 5"	1 One 2 Two at 180°	A Black B White G Verde H Bronze I Gray J Green Z Custom

Flag Holder Bracket

example: FHB411-A

Product Code FHB	Pole Dia.	# of Arms	Length 12	Finish
FHB Flag Holder Bracket	4" 5"	1 One 2 Two at 180°	12"	A Black B White G Verde H Bronze I Gray J Green Z Custom



P1150 Series

Urban Decorative Poles

Flower Pot Bracket example: FPB4212-B Product Code Pole Dia. # of Arms Length Finish FPB 12 FPB Flower Pot Bracket A Black B White G Verde H Bronze 4" 5" 1 One 2 Two at 180° 12" I Gray J Green Z Custom




Street Sign Holder

example: SS5942-A

Product Code SS	Pole Dia.	Sign Height	Sign Length	Finish
SS Street Sign Holder	4" 5"	6" 9"	24" 30" 36" 42"	A Black B White G Verde H Bronze I Gray J Green Z Custom





Other Adapters & Accessories

Other	Adapters & Accessories	example: M0004-A	
Product	Code	Finish	
M0004 M0005 M0080	Button Eye Photocell - 120V Button Eye Photocell - 208V, 240V 9-1/2" dia. Pier Base w/ 3" O.D. tenon, 7" bolt circle	A Black B White G Verde H Bronze I Gray J Green Z Custom	

P1150 Series

Urban Decorative Poles

Specifications

Housing

6000 series extruded aluminum alloy.

Anchor Base

356 HM high-strength, low-copper, proprietary cast aluminum alloy. Anchor rods are hot dipped galvanized steel.

Finish

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, or to match other standard Signify brand finishes such as those from Lumec, Gardco, or the discontinued Hanover brand, contact the factory for more information as most special requests can be accommodated.

Warranty

Hadco aluminum poles are covered by a 5-year structural and finish warranty. Some exceptions apply. For more information visit signify.com/warranties

Outlets

Standard Duplex Outlet (D) includes a universal color-matched metal weatherproof cover. Weatherproof while in use. Heavy-duty allmetal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Maximum 15A output.

GFI Duplex Outlet (G) includes a dual-function indicator light and universal color-matched metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. Maximum 15A output.

Buy American Act of 1933 (BAA)

This product is manufactured in one of our US factories and, as of the date of this document, this product was considered a commercially available off-the-shelf (COTS) item meeting the requirements of the BAA. This BAA designation hereunder does not address (i) the applicability of, or availability of a waiver under, the Trade Agreements Act, or (ii) the "Buy America" domestic content requirements imposed on states, localities, and other non-federal entities as a condition of receiving funds administered by the Department of Transportation or other federal agencies. Prior to ordering, please visit www.signify.com/baa to view a current list of BAA-compliant products to confirm this product's current compliance.

General Pole Information

Design

EPA specs conform to AASHTO 2001 standard. The poles as charted are designed to withstand dead loads and predicted dynamic loads developed by variable wind pressure with an additional 2.5 gust factor under the following conditions: The charted weights include luminaire(s) and/or mounting bracket(s). Poles installed in areas of known abnormal conditions may require special consideration. For example: coastal areas, airports, and areas of special winds. Poles are designed for ground mounted applications. Poles mounted on structures (such as buildings and bridges) may also necessitate special consideration requiring Hadco's recommendation. Height correction factors and drag coefficients are applied to the entire structure. An appropriate safety factor is maintained based on the minimum yield strength of the material incorporated in the pole.

Warnings

This design information is intended as a general guideline only. The customer is solely responsible for proper selection of pole, luminaire, accessory, and foundation under the given site conditions and intended usage. The addition of any items to the pole, in addition to the luminaire, will dramatically impact the EPA load on that pole. It is strongly recommended that a qualified professional be consulted to analyze the loads given the user's specific needs to ensure proper selection of the pole, luminaire, accessories, and foundation. Hadco assumes no responsibility for such proper analysis or product selections. Failure to ensure proper site analysis, pole selection, loads and installation can result in pole failure, leading to serious injury or property damage.

(s)ignify

© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.