



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

Complete Fixture consists of Reflector Trim & Frame-In Kit. Select each separately.

2000P1	Reflector Trims — See Individual Reflector Trim Specification Sheets						
	Open Downlight				Recessed		Enclosed
Frame-In Kit	Aperture Cone	Satin Cone	Baffles	Pinhole	Adjustable	Eyeball	Diffuser
	2012 2012NM 2013 2013BKNM 2013CD 2013CDNM 2013NM 2013BK 2013WH 2013WD 2013WDP	2008 2008NM 2010 2010NM	2005 2005BNM 2005NM 2005WH	2011	2027 2022WH 2027NM 2027WH 2029BK 2029BKNM 2029CD 2029CDNM 2029CL 2029CLNM 2029GD 2029GDNM 2029WH 2027BNM	2022 2022WH	2090

### Features

- Housing:** .032" aluminum. Access door for inspection of junction box.
- Mounting Frame:** .036" (#20 ga.) galvanized steel. Accommodates all ceilings up to 1" thick. Push-in/twist-out rotoclips hold reflector flush to ceiling.
- Junction Box:** 4" x 3 1/2" x 2"; .063 (#14 ga.) galvanized steel. U.L. listed for maximum of 8 No. 12 ga. 75° C through branch circuit conductors. Access door inside of housing allows easy inspection of wiring without removal of housing. Integral cable clamps permit attachment of nonmetallic Romex® or armored cable without need of additional connectors.
- Mounting Bars:** .059 (#16 ga.) galvanized steel. 13" long bars extend to 27" with integral nailing tabs. Attaches to wood joist without need of accessories.
- Socket Spring:** .030" steel.
- Socket:** Porcelain medium base; nickel plated screw shell. Pre-wired with #18 ga. SF1 leads to junction box.
- Thermal Protector:** Meets NEC and UL requirements. Insulation must be kept 3" away from fixture sides and wiring compartments and must not be placed above fixture in a manner which will entrap heat.

# 2000P1 Lytecaster INC 3 3/4"

## Performance Non-IC Frame

### Options & Accessories

<b>Mounting Bars:</b>	<b>1964</b> - 20" set of (4)
<b>T-Bar Ceiling Clips:</b>	<b>1956</b> - set of (4)
<b>Plaster Ceiling Ring:</b>	<b>1959</b> - 7/8" depth for wet plaster ceilings
<b>277V Remote Step Down Transformer:</b>	<b>7997</b> - 277V down to 120V 300W max. load.

### Labels

UL (Suitable for Damp Locations), I.B.E.W.

Romex® is a registered trademark of General Cable Industries Inc.

Romex® is a registered trademark of General Cable Industries Inc.

