
LIGHTOLIER

Gimbal Ring PAR30 & PAR38

Track Lighting

by (s) ignify

55215, 55241, 55242



Project: Location Cat.No: Туре: Lamps: Qty: Notes:

Line Voltage PAR38 Ring

Catalog No Lamp

55215WH White 55215BK Black

250W PAR38

Features

- 1. Lamp Shield: 0.040" (1.02mm) steel.
- 2. Pivot Mounting: Tensioned with integral spring washer. Adjusts vertically up to 180°.
- 3. Socket Housing: Molded polycarbonate. Integral color.
- 4. Yoke: 0.093" (2.36mm) steel.
- 5. Pivot Mounting: Permanently tensioned. Adjust horizontally with 350° stop.
- 6. Polarity Keyway.
- 7. Movable Contact: Solid Brass. Extends for connection to 2nd circuit in Advent Lytespan track.
- 8. Push Tab: Molded polycarbonate. Detaches unit.
- 9. Lytespan Attachment Fitting: Molded polycarbonate. Integral color. Fitter twists onto track, lock on with push tab.
- 10. Lamp Retaining: 0.018" (0.46mm) spring steel.
- 11. Ground Contact: Solid brass.
- 12. Socket: Porcelain socket body, medium base nickel plated screw shell. 18AWG, SEW-1 (150°C-300V) leads.

All Basic (single circuit), Advent (2 circuits) track systems, Monopoint and Multipoint.

Accessory

0087: Accessory Holder (3 clips) Accept maximum of one accessory 4 3/4" (121mm) dia. (ADF4, AF4 and AL4 series)




All painted finishes are baked powder or enamel.


Marking

CSA Cerified, suitable for dry locations only.

55215, 55241, 55242 Gimbal Ring

Track Heads (PAR30 & PAR38)





Line Voltage PAR30 Ring Front Relamping

Catalog No. Lamp

55241WH White Black 55241BK

75W PAR30S (Short Neck Lamp)

Features

- 1. Lamp Shield: 0.040" (1.02mm) steel.
- 2. Pivot Mounting: Tensioned with integral spring washer. Adjusts vertically up to 180°.
- 3. Socket Housing: 0.030" (0.76mm) steel.
- 4. Yoke: 0.093" (2.36mm) steel.
- 5. Pivot Mounting: Permanently tensioned. Adjust horizontally with 350° stop.
- 6. Polarity Keyway.
- 7. Movable Contact: Solid brass. Extends for connection to 2nd circuit in Advent track.
- 8. Push Tab: Molded polycarbonate. Detaches unit.
- 9. Lytespan Attachment Fitting: Molded polycarbonate. Integral color.

Fitter twists onto track, lock on with push tab.

- 10. Lamp Retaining: 0.018" (0.46mm) spring steel.
- 11. Ground Contact. Solid brass.
- 12. Socket: Porcelain body, medium base, nickel plated screw shell. 18AWG, SEW-1, 150°C leads.

Mounting

All Basic (single circuit), Advent (2 circuits) track systems, Monopoint and Multipoint.


All painted finishes are baked powder or enamel.

Marking

cCSAus Cerified, suitable for dry locations only.

55215, 55241, 55242 Gimbal Ring

Track Heads (PAR30 & PAR38)



Line Voltage PAR38 Ring Front Relamping

Catalog No. Lamp

55242WH White **55242BK** Black

250W PAR38

Features

- 1. Lamp Shield: 0.040" (1.02mm) steel.
- 2. Pivot Mounting: Tensioned with integral spring washer. Adjusts vertically up to 180° .
- 3. Socket Housing: 0.030" (0.76mm) steel.
- 4. Yoke: 0.093" (2.36mm) steel.
- 5. Pivot Mounting: Permanently tensioned. Adjust horizontally with 350° stop.
- 6. Polarity Keyway.
- 7. Movable Contact: Solid brass. Extends for connection to 2nd circuit in Advent track.
- 8. Push Tab: Molded polycarbonate. Detaches unit.
- **9. Lytespan Attachment Fitting:** Molded polycarbonate. Integral color. Fitter twists onto track, lock on with push tab.
- 10. Lamp Retaining: 0.018" (0.46mm) spring steel.
- 11. Ground Contact. Solid brass.
- 12. Socket: Porcelain body, medium base, nickel plated screw shell. 18AWG, SEW-1, 150°C leads.

Mounting

All Basic (single circuit), Advent (2 circuits) track systems, Monopoint and Multipoint.

Finish

All painted finishes are baked powder or enamel.

Marking

cCSAus Cerified, suitable for dry locations only.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation 400 Crossing Blvd, Suite 600 Bridgewater, NJ 08807 Telephone: 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Telephone: 800-668-9008

Il trademarks are owned by Signify Holding or their respective owners.