



Ordering guide

Example: DB21 A A0 12L E

LED Product Code	Finish	Optics	Wattage	Voltage
DB21		A0	12L	E
DB21 Alluminum Bollard	A Black H Bronze	A0 Symmetric	12L 9.5W LED	E 120V

Incandescent Product Code	Finish
DB21	
DB21 Aluminum Bollard	A Black H Bronze

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____

Specifications

Housing

356 HM high-strength, low-copper, proprietary cast aluminum alloy. Dome rood with die-cast aluminum louvers. Easy access to lamp. 5" diameter extruded aluminum with a wall thickness of 0.125". All non-ferrous fasteners prevent corrosion and ensure longer life.

Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Optional CraftStone™ finish is highly weather-resistant and bonded to the aluminum substrate. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

Optical Assembly

Symmetric. Die-cast aluminum louvers with underside painted with highly reflective white powdercoat. Tempered glass globe.

Lamping

LED 4Kv medium base porcelain socket A19.
Incandescent medium base A19.

Electrical Assembly

LED is 2700K warm white, delivers 800 lumens, and is dimmable. Lamp life is rated at 25,000 hours. 120V only. 4Kv rated medium base porcelain socket. Key-slotted ballast assembly is mounted to an aluminum plate, which is mounted inside the base. Quick disconnects for easy installation and removal. 4Kv rated medium based porcelain socket. Nickel-plated screw shell with center contact.

Installation & Mounting

Tube is mounted to the base plate with three (3) 5/16-18 flat head allen key stainless steel tamper-resistant screws.

Warranty

Three-year limited warranty.

Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height 21" (53cm)	Width 6" (15cm)	Bolt Circle 3" (8cm)
Base Diameter 5" (13cm)	Anchor Rods Internal (3) 3/8" dia. x 8" long (1cm x 20cm)	Max Weight Powdercoat: 13lbs CraftStone: 17lbs

