



Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering guide

Example: DB30 A A0 12L E

Product Code	Finish		Optics	Wattage		Voltage
<b>DB30</b>			<b>A0</b>			
DB30 Aluminum Bollard	A H	Black Bronze	A0 Symmetric	12L 100I	9.5W LED 100W INC	E 120V

### Specifications

#### Housing

356 HM high-strength, low-copper, proprietary cast aluminum alloy. Dome roof with die-cast aluminum louvers. Easy access to lamp. 5" dia. extruded aluminum with a wallthickness of 0.125". All non-ferrous fasteners prevent corrosion and ensure longer life.

#### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more

#### Optical Assembly

Symmetric. Die-cast aluminum louvers with underside painted with highly reflective white powdercoat. Tempered glass globe.

#### Lamping

- LED 4Kv medium base porcelain socket A19.
- Incandescent Medium Base A19.

#### Electrical Assembly

LED is 2700K warm white, delivers 800 lumens, and is dimmable. Lamp life is rated at 25,000 hours. 120 volt only. 4Kv rated medium base porcelain socket. Key-slotted Ballast Assembly is mounted to an aluminum plate, which is mounted inside the base. Quick disconnects for easy installation and removal. 4kv rated medium base porcelain socket. Nickel-plated screw shell with center contact.

#### Installation & Mounting

Tube is mounted to the base plate with three (3) 5/16-18 flat head allen key stainless steel tamper-resistant screws.

#### Warranty

Three-year limited warranty.

#### Certifications

ATL listed to U.S safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

#### Height

30" (74cm)

#### Width

6" (15cm)

#### Bolt Circle

3" (8 cm)

#### Anchor Rods

Internal (3) 3/8" dia. x 8" long (1 cm x 20cm)

#### Base Diameter

5" (13cm)

#### Max. Weight

Powdercoat: 15 lbs

#### Max. Weight

CraftStone: 19 lbs

