



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Catalog No.	Finish	Mounting	Dimensions
7599	Matte White	All Lightolier Track Systems	Height 3"
7599BK	Black	(Basic & Advent)	Dia. 1 1/16"

Features

- Attachment Fitting:** Die-cast zinc alloy. Matte white or black finish.
- Stem Locking Clamps/Electrical Contacts:** Move in conjunction with lever.
- Screw Terminal:** Connects onto individual conductors.
- Movable Brass Contact:** Extends for connection to 2nd circuit in Advent Lytespan Track.
- Polarity Keyway**
- Lever:** Energizes unit
- Ground Screw/Ground Clip**
- Strain Relief Cap:** Machined brass. 1/4-18 I.P. internal thread for connecting stem or chain loop.
- Cord Protective Nylon Bushing:** Prevents damage to fixture cord.
- Fixture Cord, Stem or Chain:** Note: Cord max dia. .340" (not sup-plied).
Stem size: 1/2" O.D., .065" wall, 1/4-18 I.P. thread (not sup-plied).
Chain: 1/4-18 I.P. thread (not supplied).

- #8-32 Hex Head Set Screw:** Allen wrench provided.
- Insulator Housing:** .032" plastic.
- Conductor:** #18 ga. max.
- Ground Spring**
- Nylon Bushing:** Used with pendant cord.
- 1/4" - 20 Set Screw:** Secures fixture cord, stem or chain loop.

Electrical

Can be used with 3 conductor fixture cords up to a maximum diameter of 0.340 suitable for 2 conductor and 3 conductor stem or chain mounted fixtures.

Finish

All painted finishes baked enamel.

Labels

UL; I.B.E.W.

