



## Ordering guide

Example: DB14 A A0 12L E

| LED Product Code                  | Finish              | Optics                          | Wattage                          | Voltage                        |
|-----------------------------------|---------------------|---------------------------------|----------------------------------|--------------------------------|
| <input type="text" value="DB14"/> |                     | <input type="text" value="A0"/> | <input type="text" value="12L"/> | <input type="text" value="E"/> |
| DB14 Aluminum Bollard             | A Black<br>H Bronze | A0 Symmetric                    | 12L 9.5W LED                     | E 120V                         |

| Incandescent Product Code         | Finish              |
|-----------------------------------|---------------------|
| <input type="text" value="DB14"/> |                     |
| DB14 Aluminum Bollard             | A Black<br>H Bronze |

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

## Specifications

### Housing

356 HM high-strength, low-copper, proprietary cast aluminum alloy. Dome roof with die-cast aluminum louvers. Easy access to lamp. 5" dia. extruded aluminum with a wall thickness of 0.125". All non-ferrous fasteners prevent corrosion and ensure longer life.

### Finish

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

### Optical Assembly

Symmetric. Die-cast aluminum louvers with underside painted with highly reflective white powdercoat. Tempered glass globe.

### Lamping

LED and incandescent medium base A19.

### Electrical Assembly

LED is 2700K warm white, delivers 800 lumens and is dimmable. Lamp life rates at 25,000 hours. 120 volt only. LED and incandescent have 4kv rated medium base porcelain socket. Nickel-plated screw shell with center contact.

### Installation & Mounting

Tube is mounted to the base plate with three (3) 5/16-18 flat head allen key stainless steel tamper-resistant screws.

### Warranty

Three-year limited warranty.

### Certifications

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 standards.

| Height        | Width   | Bolt Circle                            |
|---------------|---|--|
| 14" (36cm)    | 6" (15cm)                                     | 3" (8cm)                               |
| Base Diameter | Anchor Rods                                   | Max Weight                             |
| 5" (13cm)     | Internal (3) 3/8" dia. x 8" long (1cm x 20cm) | Powdercoat: 10lbs<br>CraftStone: 14lbs |

