

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: HFP210 P4 A N PM

|                       |                            |  |
|-----------------------|----------------------------|--|
| <b>Product Code</b>   | HFP210                     | Single   |
| <b>Post diameter</b>  | P4                         | 4" Post Mount                                      |
| <b>Finish</b>         | A<br>B<br>G<br>H<br>I<br>J | Black<br>White<br>Verde<br>Bronze<br>Gray<br>Green |
| <b>Arm Accessory</b>  | N                          | None   |
| <b>Post Machining</b> | PM                         | Post Machining                                     |

### Specifications

**HOUSING:**

6063-T6 Extruded aluminum .

**FINISH:**

Thermoset polyester powdercoat is electrostatically applied after a five-stage conversion cleaning process and bonded by heat fusion thermosetting. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B117 specifications. For larger projects where a custom color is required, contact the factory for more information.

**WARRANTY:**

Three-year limited warranty.

**Height :**

35" (89 cm)

**Length:**

26 3/4" (68 cm)

**Internal Slip Fitter Height:**

15.5" (39 cm)

**Internal Slip Fitter Diameter:**

3 1/2" (9 cm)

**EPA:**

2.30 sq. ft.

