


Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

Ordering Guide

Example: P5092 12 I

Product Code	P5092	
Pole Height	12	12'
	14	14'
	16	16'
Finish	I	Gray
	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green



Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 6063-T6 Extruded aluminum . Anchor rods are hot dipped galvanized steel . Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

CERTIFICATIONS:

Manufactured to ISO 9001:2008 Standards.

WARRANTY:

Three-year limited warranty.

P5092 P5092

Pole

Specifications

Tenon/Top:

3" OD

Bolt Circle:

8" - 13"

Anchor Rods:

(4) 3/4" dia. x 19"

Base Dimensions:

17" dia. x 21"

Hand Hole :

4 1/2" x 5"

Shaft:

6" to 4" Tapered Fluted

Wall Thickness:

0.188 Aluminum

Height :

12', 14', 16'

