

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_


Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: P195 12 A T D

| Product Code                      | P195 |   |
|-----------------------------------|------|---|
| <b>Pole Height</b>                | 12   | 12'   |
|                                   | 14   | 14'   |
|                                   | 15   | 15'   |
|                                   | 16   | 16'   |
|                                   | 18   | 18'   |
|                                   | 20   | 20'   |
| <b>Finish</b>                     | A    | Black                                       |
|                                   | B    | White                                       |
|                                   | G    | Verde                                       |
|                                   | H    | Bronze                                      |
|                                   | I    | Gray  |
|                                   | J    | Green                                       |
| <b>Outlet Location (Optional)</b> | T    | 12" Down from Top - Aligned with House Side |
| <b>Outlet Options (Optional)</b>  | D    | Standard Duplex                             |
|                                   | G    | GFI Duplex                                  |



### Specifications

**HOUSING:**

413F, Low-Copper cast aluminum. 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel.

**FINISH:**

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

**WARRANTY:**

Three-year limited warranty.

**OUTLET:**

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# P195 P195

## Pole

### Specifications

---

**Tenon/Top:**

4" OD

**Bolt Circle:**

7 1/2" - 9 1/2"

**Anchor Rods:**

(4) 3/4" dia. x 19"

**Base Dimensions:**

11 1/2" dia. x 2 3/8"

**Base Cover:**

(Included) 12 1/8" dia. x 3 1/4"

**Hand Hole :**

2" x 4" Oval

**Shaft:**

4" Straight

**Wall Thickness:**

0.188 Aluminum

**Height :**

12', 14', 15', 16', 18', 20'

### Pole EPA Values

---

| Windspeed(mph) | Height |        |        |        |        |        |
|----------------|--------|--------|--------|--------|--------|--------|
|                | 12'    | 14'    | 15'    | 16'    | 18'    | 20'    |
| 80             | 6.4500 | 4.1300 | 3.9200 | 3.3500 | 2.7200 | 2.1700 |
| 100            | 3.8800 | 2.3100 | 2.0100 | 1.8000 | 1.3400 | 0.9300 |

