

Project: \_\_\_\_\_


Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_



### Ordering Guide

Example: P1150 86 I T D

Product Code	P1150	
Pole Height	86	8' 6"
	106	10' 6"
	126	12' 6"
Finish	I	Gray
	A	Black
	B	White
	G	Verde
	H	Bronze
	J	Green
Outlet Location (Optional)	T	12" Down from Top - Aligned with House Side *1
	B	4" Up from Top of Base - Aligned with House Side
Outlet Options (Optional)	D	Standard Duplex
	G	GFI Duplex

\*1 Top outlets not available with the HFP arms.

### Specifications

**HOUSING:**

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 6063-T6 Extruded aluminum . Anchor rods are hot dipped galvanized steel .

**FINISH:**

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

**WARRANTY:**

Three-year limited warranty.

**OUTLET:**

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# P1150 P1150

## Pole

### Specifications

---

**Tenon/Top:**

3" OD

**Bolt Circle:**

7"

**Anchor Rods:**

Internal: (4) 1/2" dia. x 15"

**Base Dimensions:**

11" dia. x 30"

**Hand Hole :**

4 1/4" x 4 1/2"

**Shaft:**

4" - 3" Tapered

**Wall Thickness:**

0.125 Aluminum

**Height :**

8' 6", 10' 6", 12' 6"

### Pole EPA Values

---

Windspeed(mph)	Height		
	8'	10'	12'
80	9.0600	7.0600	5.5500
100	5.4200	4.0300	2.9500

