

Project: _____

Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: P120 8 A T D

Product Code	P120	
Pole Height	8	8'
	10	10'
	12	12'
	14	14'
Finish	A	Black
	B	White
	G	Verde
	H	Bronze
	I	Gray
	J	Green
Outlet Location (Optional)	T	12" Down from Top - Aligned with House Side
Outlet Options (Optional)	D	Standard Duplex
	G	GFI Duplex

Specifications

HOUSING:

413F, Low-Copper cast aluminum. 6063-T6 Extruded aluminum . Anchor rods are hot dipped galvanized steel .

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P120 P120

Pole

Specifications

Tenon/Top:

3" OD

Bolt Circle:

7 1/2" - 9 1/2"

Anchor Rods:

(4) 3/4" dia. x 19"

Base Dimensions:

11 1/2" dia. x 2 3/8"

Base Cover:

(Included) 12 1/8" dia. x 3 1/4"

Hand Hole :

2" x 4" Oval

Shaft:

4" - 3" Tapered

Wall Thickness:

0.125 Aluminum

Height :

8', 10', 12', 14'

Pole EPA Values

Windspeed(mph)	Height			
	8'	10'	12'	14'
80	9.7800	7.8500	6.4500	4.1100
100	6.1000	4.8200	3.6000	2.0100

