

Project: _____


Location: _____

Cat.No: _____

Type: _____

Lamps: _____ Qty: _____

Notes: _____



Ordering Guide

Example: P2565 10 A T D

| Product Code | P2565 | |
|-----------------------------------|-------|--|
| Pole Height | 10 | 10' |
| | 12 | 12' |
| | 14 | 14' |
| | 16 | 16' |
| Finish | A | Black |
| | B | White |
| | G | Verde |
| | H | Bronze |
| | J | Green |
| Outlet Location (Optional) | T | 12" Down from Top - Aligned with House Side |
| | B | 4" Up from Top of Base - Aligned with House Side |
| Outlet Options (Optional) | D | Standard Duplex |
| | G | GFI Duplex |

Specifications

HOUSING:

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 6005-T5 extruded aluminum. Anchor rods are hot dipped galvanized steel . Tenon is 356 HM sand cast aluminum.

FINISH:

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

WARRANTY:

Three-year limited warranty.

OUTLET:

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

P2565 P2565

Pole

Specifications

Tenon/Top:

3" OD

Bolt Circle:

11" - 14"

Anchor Rods:

(4) 3/4" dia. x 19"

Base Dimensions:

12 3/4 sq. x 43 3/4"

Base Cover:

(Included) 19" dia. x 9 1/4"

Hand Hole :

4 3/8" x 5 3/4"

Shaft:

4" Straight Fluted

Wall Thickness:

0.125 Aluminum

Height :

10', 12', 14', 16'

Pole EPA Values

| Windspeed(mph) | Height | | | |
|----------------|---------|---------|--------|--------|
| | 10' | 12' | 14' | 16' |
| 80 | 13.7800 | 11.2200 | 6.9700 | 5.5400 |
| 100 | 8.3400 | 6.6000 | 3.7700 | 2.7200 |

