

Product Id	Model No.	Classification
P0AXXBV	1FXP30L835-4-DS-(UNV,120,277)-DIM-(IAP)	standard
PDO9IPBS	1FXP30L835-4-DS-(UNV,120,277,347)-DIM	standard
PHW1JR5B	1FXP30L835-4-DS-347-DIM	standard
PS4ZVO99	1FXP30L835-4-DS-UNV-DIM	standard
PWP4162Z	1FXP30L840-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
P5E16H79	1FXP30L840-4-DS-(UNV,120,277,347)-DIM	standard
PTB60F5V	1FXP30L840-4-DS-347-DIM	standard
PWRV52JU	1FXP30L840-4-DS-UNV-DIM	standard
PIY6G5D5	1FXP30L840-4-DS-UNV-DIM-EMLED(7)	standard
PO5127XV	1FXP30L850-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PQIS3OFH	1FXP30L850-4-DS-(UNV,120,277,347)-DIM	standard
PNX8VM4H	1FXP38B835-4-DS-(UNV,120,277)-DIM	standard
PI4QTLAI	1FXP38B835-4-DS-347-DIM	standard
PLD0C0JP	1FXP38B835-4-DS-UNV-DIM	standard
PXXB3DQO	1FXP38B840-4-DS-(UNV,120,277)-DIM	standard
PIURCW4X	1FXP38B840-4-DS-347-DIM	standard
P55U2VR9	1FXP38B840-4-DS-UNV-DIM	standard
P6B39YOV	1FXP38B850-4-DS-(UNV,120,277)-DIM	standard
P12T3VUA	1FXP38L835-4-DS-(UNV,120,277)-DIM-(IAP)	standard
PIK3WBOY	1FXP38L835-4-DS-(UNV,120,277,347)-DIM	standard
P6P0JPV9	1FXP38L835-4-DS-347-DIM	standard
P4OOL25N	1FXP38L835-4-DS-UNV-DIM	standard
PCXGY544	1FXP38L840-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PQVI273F	1FXP38L840-4-DS-(UNV,120,277,347)-DIM	standard
PONM63TB	1FXP38L840-4-DS-347-DIM	standard
PPS2N7V4	1FXP38L840-4-DS-UNV-DIM	standard
PAIO3B4A	1FXP38L840-4-DS-UNV-DIM-EMLED(7)	standard
PL7HYVI5	1FXP38L850-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PLZL8YNS	1FXP38L850-4-DS-(UNV,120,277,347)-DIM	standard
PCRDFID0	1FXP45L835-4-DS-347-DIM	standard
P4N3B6C8	1FXP45L835-4-DS-UNV-DIM	standard
PR80OHEM	1FXP45L840-4-DS-(UNV,120,277)-DIM-(IAP)	standard
P66EZR1N	1FXP45L840-4-DS-(UNV,120,277,347)-DIM	standard
POR48I8S	1FXP45L840-4-DS-347-DIM	standard
PPUL14AT	1FXP45L840-4-DS-UNV-DIM	standard
PGQ58E8A	1FXP45L840-4-DS-UNV-DIM-EMLED(7)	standard
POQ3VCXU	1FXP45L850-4-DS-(UNV,120,277)-DIM-(IAP)	standard
PTOHU05F	1FXP45L850-4-DS-(UNV,120,277,347)-DIM	standard
P3WCIZBC	2FXP30L835-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
P6VXGPD3	2FXP30L835-2-DS-(UNV,120,277,347)-DIM	standard
P3S294F0	2FXP30L835-2-DS-347-DIM	standard
P6VC5NO4	2FXP30L835-2-DS-UNV-DIM	standard
P0ON9SJX	2FXP30L840-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PUKIJCM1	2FXP30L840-2-DS-(UNV,120,277,347)-DIM	standard
PTYWQV5Y	2FXP30L840-2-DS-347-DIM	standard
P4I58700	2FXP30L840-2-DS-UNV-DIM	standard
PNE4ML8D	2FXP30L850-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PKL2RYEP	2FXP30L850-2-DS-(UNV,120,277,347)-DIM	standard
P6C4DRW3	2FXP38B835-2-DS-(UNV,120,277)-DIM	standard
PFMLT9Q1	2FXP38B835-2-DS-347-DIM	standard
P3UFI02Q	2FXP38B835-2-DS-UNV-DIM	standard
PN9QL525	2FXP38B840-2-DS-(UNV,120,277)-DIM	standard
P9WAK471	2FXP38B840-2-DS-347-DIM	standard

Product Id	Model No.	Classification
PPJRRQF8	2FXP38B840-2-DS-UNV-DIM	standard
P8CWRH60	2FXP38B850-2-DS-(UNV,120,277)-DIM	standard
POE07IPN	2FXP38L835-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PKBJZHJU	2FXP38L835-2-DS-(UNV,120,277,347)-DIM	standard
P9YT7T0J	2FXP38L835-2-DS-UNV-DIM	standard
PYHP2SB7	2FXP38L835-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PE48DLAK	2FXP38L835-4-DS-(UNV,120,277,347)-DIM	standard
PF5SIF73	2FXP38L835-4-DS-347-DIM	standard
PO7NKNEM	2FXP38L835-4-DS-UNV-DIM	standard
PLUAVJ48	2FXP38L840-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PFMSPLCR	2FXP38L840-2-DS-(UNV,120,277,347)-DIM	standard
P5POSVCF	2FXP38L840-2-DS-347-DIM	standard
PNCNEMVS	2FXP38L840-2-DS-UNV-DIM	standard
PJHOVK2W	2FXP38L840-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PPKGR8M5	2FXP38L840-4-DS-(UNV,120,277,347)-DIM	standard
PEA1WXLW	2FXP38L840-4-DS-347-DIM	standard
PCPQXIJ7	2FXP38L840-4-DS-UNV-DIM	standard
PP1GSOFQ	2FXP38L850-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PJQYKZFK	2FXP38L850-2-DS-(UNV,120,277,347)-DIM	standard
PPBU46TX	2FXP38L850-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PKXK6XSW	2FXP38L850-4-DS-(UNV,120,277,347)-DIM	standard
P1TQFVLG	2FXP42B835-4-DS-(UNV,120,277)-DIM	standard
P5ENQ356	2FXP42B835-4-DS-347-DIM	standard
P18GLHVD	2FXP42B835-4-DS-UNV-DIM	standard
P57KUXE3	2FXP42B840-4-DS-(UNV,120,277)-DIM	standard
P38OXCUD	2FXP42B840-4-DS-347-DIM	standard
PYWJ600F	2FXP42B840-4-DS-UNV-DIM	standard
PJB4X3NZ	2FXP42B850-4-DS-(UNV,120,277)-DIM	standard
PVS1XCDD	2FXP43L835-4-DS-(UNV,120,277,347)-DIM	standard
PATZU3R2	2FXP43L835-4-DS-347-DIM	standard
P1GOI91J	2FXP43L835-4-DS-UNV-DIM	standard
PWRU9XJ1	2FXP43L840-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
P1XCVZQD	2FXP43L840-4-DS-(UNV,120,277,347)-DIM	standard
PLO3LNO0	2FXP43L840-4-DS-347-DIM	standard
PS40OQ6V	2FXP43L840-4-DS-UNV-DIM	standard
P1X3ZCL2	2FXP43L850-4-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
POY19AGP	2FXP43L850-4-DS-(UNV,120,277,347)-DIM	standard
PR5Z74GA	2FXP45L835-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PDKNW9Y9	2FXP45L835-2-DS-(UNV,120,277,347)-DIM	standard
PR53UKKN	2FXP45L840-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PHGTLCWQ	2FXP45L840-2-DS-(UNV,120,277,347)-DIM	standard
PTGZG3RF	2FXP45L840-2-DS-347-DIM	standard
PFI6H3FF	2FXP45L840-2-DS-UNV-DIM	standard
POYSTNV8	2FXP45L850-2-DS-(UNV,120,277)-DIM-(EMLED(7),IAP)	standard
PW53LL2J	2FXP45L850-2-DS-(UNV,120,277,347)-DIM	standard
P6PZL1SB	2FXP48L835-4-DS-UNV-DIM	standard
P60BOUUK	2FXP48L840-4-DS-(UNV,120,277)-DIM-(IAP)	standard
PD2LN1IW	2FXP48L840-4-DS-(UNV,120,277,347)-DIM	standard
PCU4EALV	2FXP48L840-4-DS-347-DIM	standard
PLNNX6R5	2FXP48L840-4-DS-UNV-DIM	standard
PZJJQY9Y	2FXP48L850-4-DS-(UNV,120,277)-DIM-(IAP)	standard
P6E74AVJ	2FXP48L850-4-DS-(UNV,120,277,347)-DIM	standard
P2NOR332	2FXP54L840-4-DS-(UNV,120,277)-DIM-(IAP)	standard

11/6/2019

Information as of this date. Please check the DLC QPL for confirmation (www.designlights.org/QPL).

Product Id	Model No.	Classification
POWE9RVL	2FXP54L840-4-DS-(UNV,120,277,347)-DIM	standard
P460EY9R	2FXP54L840-4-DS-347-DIM	standard
P46UXBMY	2FXP54L840-4-DS-UNV-DIM	standard
P4XNNOKU	2FXP54L850-4-DS-(UNV,120,277)-DIM-(IAP)	standard
PQGOTB7F	2FXP54L850-4-DS-(UNV,120,277,347)-DIM	standard
PV4YZHLZ	2FXP60L840-4-DS-347-DIM	standard
P7ZUH7J6	2FXP60L840-4-DS-UNV-DIM	standard