

LIGHTOLIER

by  Signify

Track Lighting

OmniSpot LED

LC 600lm, 1000lm, 2000lm



The smooth, contemporary style takes accent lighting designs from subtle to bold by eliminating the need for a visible heat sink. OmniSpot's driver is integrated directly in the housing for a sleek, compact look. OmniSpot is also the only track luminaire to feature a sleek side mounted arm that attaches easily to almost any manufacturer's track system, and provides less than one inch of space between the track head and track system.

Small is the new big

The best things in life come in small packages, and Lightolier OmniSpot LED track luminaires are no exception. OmniSpot track luminaires combine compact with power to keep attention focused exactly on designated areas of interest.

Benefits

- Industry leading center beam candlepower at 2000lm 11° Narrow Spot, delivering impactful performance
- Integrated design allows for a quiet, uncluttered ceiling
- Side arm enables closest fit to track for an unobtrusive look and balanced design aesthetic
- Increased lighting design flexibility with field changeable optics and available accessories

CrispWhite technology

Available in 90CRI/3000K only, the Lumileds 90CRI CrispWhite technology combines the warm, saturated colors of high CRI with crisp and vibrant whites. The small form factor and high quality of light make this an impactful option for retail display areas.

PremiumColor technology

Available in 90CRI/3000K only, provides vivid and robust colors that pop while maintaining a strong ambient white and bold black balance in any space. This LED technology is sure to add positive energy to varying application needs.



LC OmniSpot LED

600lm, 1000lm, 2000lm track lighting



Features

Efficacy: Up to 108lm/W
Lumens: 600, 1000, 2000
Watts: 6, 12, 25
CRI: 80, 90 (min)
CCT: 2700K, 3000K, 3500K, 4000K, and CrispWhite
Volts: 120V (50/60Hz)
Dimming: ELV
Beams: 11/12°, 18°, 24°, 36° (field changeable optics)
Lifetime: 50,000 hrs
Accessories: Snoot, Hex Cell, Diffusion Films
Labels: AirSeal, IC rated, RoHS & Title24 compliant, cULus wet location listed (covered ceilings only), ENERGY STAR® certified.
Warranty: 5 year limited

Excellent beam control and aesthetics combined with high performance make it ideal for accent lighting in retail and commercial applications.

Don't let OmniSpot's compact size fool you; it dominates the track lighting market with industry-leading center beam candlepower (CBCP) along with efficacy up to 108lm/W. No other available track luminaire can perform at this level in such a small form factor – all so that you can make a giant impression, encourage spending and provide a lasting positive experience. Omnispot combines compact design with powerful performance.

Fixture Complete product = Fixture + Reflector + Optional Accessory example: LC10930ALTECW

Series	Adapters	Lumens	CRI/CCT	Finishes ¹	Dimming	Options
LC	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	TE	<input type="checkbox"/>
LC OmniSpot LED cylinder track head	– Lightolier H Halo J Juno C Capri ² P Prospec ² GT Global TEK	06 600lm 10 1000lm 20 2000lm	827 80CRI/2700K 830 80CRI/3000K 835 80CRI/3500K 840 80CRI/4000K 927 90CRI/2700K 930 90CRI/3000K	AL Alum ² BK Black W White	TE Trailing edge (ELV)	– None (leave blank)
			930 90CRI/3000K	AL Alum ² BK Black W White	TE Trailing edge (ELV)	CW CrispWhite PC PremiumColor ³


Reflector example: LLMRNS

Series	Beam spreads
<input type="checkbox"/>	<input type="checkbox"/>
LLM for 600/1000lm	RNS 11°/12° Narrow Spot ⁴ RS 18° Spot RNF 24° Narrow Flood RF 36° Flood
LLAV11 for 2000lm	

Accessories⁵ example: LC10AHWH

Series	Type/Finish
<input type="checkbox"/>	<input type="checkbox"/>
Diffusion films	SY Symmetrical Spread SF Soft Focus LS Linear Spread FR Frosted Etched
Snoots	AL Aluminum WH Matte White BK Matte Black
LC10SN 600lm & 1000lm LC20SN 2000lm	
Accessory holders⁶	AL Aluminum WH Matte White BK Matte Black
LC10AH 600lm & 1000lm LC20AH 2000lm	
Hex cell louvers⁷ (matte black only)	
7472 600lm & 1000lm LC20HC 2000lm	

- Black and White are a matte finishes.
- Capri (C) and Prospec (P) adapters are not available in aluminum finish.
- Beam spread is 16° when PremiumColor is used with LLMRNS.
- Reflector LLM has a 12° Narrow Spot and LLAV11 has a 11° Narrow Spot.
- Aperture ring on the fixture can hold a maximum of 1 film and 1 snoot.
- Accessory holder can hold a maximum of 1 hex cell, 1 film, and 1 snoot.
- Hex cell louver needs to be ordered with an Accessory holder.



Visit Signify.com/warranties for more information on Signify's standard 5-year limited warranty.

See specification sheet LC for additional drawings and technical information.

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

