



Inspired by movement / Inspired by the splendor of movement, the **Capella** is one of the most adaptable luminaires on the market. With it's graceful curves and sweeping lines it contributes to the beautification of any environment and enhances the visual impact of any project.

Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

CPLM


Ordering guide sample

Luminaire	Lamp	Optical System	Voltage	Options	Finish*
CPLM	250 HPS	TH2F	120	HS	NP

The specially formulated Lumital powder coat finish is available in a range of many standard colors.
 * Consult LumeC's Color Chart for complete specifications.

Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.



FLAT LENS OPTICS

Weight: 47 lbs (21.3 kg)

EPA: 0.83 sq. ft.

SAG LENS OPTICS

CPLM-CPLS Urban

Capela Series

Lamp / HID

Wattage	TH2 / TH3	TH2F / TH3F
50 MH, medium	■	■
70 MH, medium	■	■
100 MH, medium	■	■
150 MH, medium	■	■
200 MH, mogul	■ ³	■ ³
320 MH, mogul	■	■ ²
175 PSMH, mogul	■	N/A
250 PSMH, mogul	■	■ ²
400 PSMH, mogul	■	N/A
35 HPS, mogul	■	■
50 HPS, mogul	■	■ ¹
70 HPS, mogul	■	■ ¹
100 HPS, mogul	■	■ ¹
150 HPS, mogul	■	■ ¹
200 HPS, mogul	■	■
250 HPS, mogul	■	■
400 HPS, mogul	■	■

■ Available. N/A: Not available.

1. Use only with ED17 medium base lamp.
2. Use only with short version LCL 5-3/4" of T15 mogul base lamp.
3. Use only with short version LCL 5" of T15 mogul base lamp.

Optical System / HID

(Lamps not included)



FLAT LENS optics

Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a flat tempered-glass lens.

TH2F Full cut-off (II)

TH3F Full cut-off (III)



SAG LENS optics

Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a sagged tempered-glass lens.

TH2 Cut-off (II)

TH3 Cut-off (III)

Voltage

HID
120
208
240
277
347
480

Options

HS House shield

PH8 Quarter-turn photoelectric cell

SAR Short arm for round pole
(E.P.A.: 0.25 sq. ft. / Weight: 2.6 lbs (1.2 kg))

CPLM-CPLS Urban

Capela Series

CPLS


Ordering guide sample

Luminaire CPLS	Lamp 150 HPS	Optical System 2HF	Voltage 120	Options PH7	Finish* NP
--------------------------	------------------------	------------------------------	-----------------------	-----------------------	----------------------


The specially formulated Lumital powder coat finish is available in a range of many standard colors.
* Consult Lumec's Color Chart for complete specifications.

Luminaires

Conform to the UL 1598 and CSA C22.2 No. 250.0-08 standards.



FLAT LENS OPTICS



SAG LENS OPTICS

Weight: 30 lbs (13.6 kg)

EPA: 0.47 sq. ft.

Lamp / HID

Wattage	TH2 / TH3	TH2F / TH3F
50 MH, medium	■	■
70 MH, medium	■	■
100 MH, medium	■	■
150 MH, medium	■	■
175 MH, medium	■	■
35 HPS, medium	■	■
50 HPS, medium	■	■
70 HPS, medium	■	■
100 HPS, medium	■	■
150 HPS, medium	■	■

■ Available. N/A: Not available.

Optical System / HID

(Lamps not included)



FLAT LENS optics

2HF Full cut-off (II)

Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a flat tempered-glass lens.



SAG LENS optics

TH2 Cut-off (II)

Sealed optical chamber consisting of an hydroformed reflector permanently sealed on a sagged tempered-glass lens.

Voltage

HID
120
208
240
277
347
480

Options

HS House shield

PH Photoelectric cell

CPLM-CPLS Urban

Capela Series

Assembly examples

