

Day-Brite

CFI

by  Signify

Industrial Linear

FCX

Value high bay



For real savings

Day-Brite / CFI FCX LED value high bay luminaires make it so easy for you to bring your commercial or industrial space into the future.

With its low profile and durable design, you might overlook the efficiency and great price, but take a second look. The value high bay really has it all. Ideal for your mid-to high ceiling applications, this sturdy luminaire comes in two sizes, with lumen outputs up to 22,000 and standard 0-10V dimming.

Take the easy route to your next lighting upgrade, with the FCX value high bay.



FCX LED value high bay

Industrial linear indoor luminaire

Easy upgrade, easy install

- Die formed sheet metal housing and end plates.
- Corrosion resistant gloss white paint after fabrication finish.
- V-hooks and 48" chains supplied (set of 2) for installation.
- Lumen maintenance up to 70% (L70) at 50,000 hours.
- Access plate located on top of housing for easy wiring.
- cULus listed for use in damp locations up to 40C ambient.
- Components are RoHS compliant.




Ordering guide

Example: FCX15L840-UNV-DIM

Series	Lumens ¹ (nominal)	Color Temp. (K)	Voltage	Dimming
FCX		840 –	–	DIM
FCX Value high bay	15L 15,000 nominal delivered lumens 22L 22,000 nominal delivered lumens	840 80 CRI, 4000K	UNV Universal voltage 120-277V 347 347V	DIM 0-10V

1. Nominal delivered lumens at 25°C ambient.

Many luminaire components, such as reflectors, lenses, sockets, lampholders, and LEDs are made from various types of plastics which can be adversely affected by airborne contaminants. If sulfur based chemicals, petroleum based products, cleaning solutions, or other contaminants are expected in the intended area of use, consult factory for compatibility.



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

