



Project: _____
Location: _____
Cat.No: _____
Type: _____
Lamps: _____ Qty: _____
Notes: _____

Ordering Guide

Example: IBH 351

Product Code	IBH	Remote Ballast
Wattage	351	(1) 35W MH
	501	(1) 50W MH
	701	(1) 70W MH
	1001	(1) 100W MH
	1501	(1) 150W PMH

Specifications

HOUSING:

Housing and cover are compression molded fiberglass reinforced polyester composite material. Fasteners are 300 series stainless steel. Gasketing is silicone. Two (2) 3/4" NPS threaded conduit inlets on bottom. Two (2) additional inlets may be field drilled and tapped.

FINISH:

Composite is textured, pressure formed, molded-in-color.

ELECTRICAL ASSEMBLY:

Standard 120-277VAC multi-tap. 50/60Hz input. Consult factory for details.

BALLAST:

All metal halide HID ballasts are core and coil and regulated with power factors better than 90% (HPF). Ballast provides +/- 5% lamp power regulation with +/- 10% input voltage regulation. Ballasts are factory pre-wired and tested. Metal halide ballasts are capable of starting at -20° F or -30° C. Ballast is encapsulated in epoxy resin for moisture resistance and additional corrosion protection. Long range ignitor included as standard equipment.

INSTALLATION & MOUNTING:

Consult factory if cover needs machined. Lower housing may be recessed directly in the ground or in concrete. Re-enterable encapsulant included as potting compound for sealing conduit entries.

WARRANTY:

Three-year limited warranty.

CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

Height :

12 1/4"

Width:

9 5/8"

