


Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Ordering Guide

Example: P5020 12 I T D

Product Code	P5020		
<b>Pole Height</b>	12	12'	*1
	14	14'	
	16	16'	
	18	18'	
<b>Finish</b>	I	Gray	
	A	Black	
	B	White	
	G	Verde	
	H	Bronze	
	J	Green	
<b>Outlet Location (Optional)</b>	T	12" Down from Top - Aligned with House Side	
	B	4" Up from Top of Base - Aligned with House Side	
<b>Outlet Options (Optional)</b>	D	Standard Duplex	
	G	GFI Duplex	

\*1 Wall thickness is 0.125 aluminum



### Specifications

**HOUSING:**

356 HM high-strength, low-copper, proprietary cast aluminum alloy . 6063-T6 Extruded aluminum . Anchor rods are hot dipped galvanized steel .

**FINISH:**

A durable polyurethane enamel finish is applied after assemblies are shot blasted to create a surface profile which allows for the highest level of paint adhesion. Laboratory tested for superior weatherability and fade resistance in accordance with ASTM B-117-64 and ANSI/ASTM G53-77 specifications. For larger projects where a custom color is required, contact the factory for more information.

**CERTIFICATIONS:**

Manufactured to ISO 9001:2008 Standards.

**WARRANTY:**

Three-year limited warranty.

**OUTLET:**

Standard Duplex Outlet has universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant. GFI Duplex Outlet has dual-function indicator light, universal metal weatherproof cover. Weatherproof while in use. Heavy-duty all-metal construction. Lockable security cover. Meets NEC 406.9 (B). Weather resistant.

# P5020 P5020

## Pole

### Specifications

---

**Tenon/Top:**  
3" OD

**Bolt Circle:**  
8" - 13"

**Anchor Rods:**  
(4) 3/4" dia. x 19"

**Base Dimensions:**  
17" dia. x 21"

**Hand Hole :**  
4 1/2" x 5"

**Shaft:**  
5" to 3" Tapered

**Wall Thickness:**  
0.188 Aluminum

**Height :**  
12', 14', 16', 18'

### Pole EPA Values

---

Windspeed(mph)	Height			
	12'	14'	16'	18'
80	13.7700	9.4000	7.7900	6.8000
100	8.1200	5.4700	4.3000	3.6700

