

# LUMEC

by  Signify

Tunnel

TunnelView

TULS/TULM/TULL



## Tunnels demand reliable solutions with maximum durability

With TunnelView, savings add up quickly due to fast, simple installation, partnered with significantly less and easier servicing than traditional products, which helps minimize costly traffic disruptions.





# TULS/TULM/TULL TunnelView

## Tunnel and underpass luminaire

### Stainless steel screws –

All exposed screws are stainless steel with ceramic primer seal for high resistance to corrosion

### Glass lens –

Offers IK09 impact protection

### Optional Tool-less latches –

For easy access

### Heat sink –

Built into the housing, ensures high efficacy and superior cooling by natural convection air flow pattern, always close to LEDs and driver optimizing their efficiency and life

### LEDs + Lens –

High performance optics optimized for maximum spacing, target lumens, and lighting uniformity

### Metal core board –

Ensures greater heat transfer and longer lifespan

### Service Tag –

Signify's innovative way to provide assistance throughout the life of the product



### Additional features –

- Three sizes for application flexibility
- Lumen output ranges from 1,700 to 53,900
- Efficacy up to 144 LPW
- Nine optical distributions for maximum versatility
- Color temperatures in 2700K, 3000K, or 4000K
- Swivel, slipfitter, or seven fixed mounting brackets available
- Controls options: DALI, Sensor Ready, Dimming
- Finish available in black, bronze, or gray

### SR Driver & Sensor Receptacle –

Optional to add flexibility for now or in the future, luminaires ship with a protective cap



### Secured door –

Door is removable and secured with tether to prevent accidental dropping or disengagement

### Durable construction –

Rugged, low copper die-cast aluminum housing for maximum durability in harsh environment

### Gasketing –

IP66 rated luminaire



The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008